

M12 MALE FLANGE PLUG A CODED REAR MOUNT

PP-wires 12x0,14 1.0m

Flange male
M12, 12-pole
Rear mounting
with multi-strand wire

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 19165

General data

Pollution Degree	3
Material (contact)	Copper alloy
Material (contact surface)	Au
Temperature range	-25...+85 °C

Cables

Cable number	979
No./diameter of wires	12× 0.14 mm²
Wire isolation	PP (br, bl, wh, gn, pk, ye, bk, gr, rd, vi, grpk, rdbl)
Outer Ø	1.25 mm ±5%
Bend radius (fixed)	5× outer Ø
Bend radius (moving)	15× outer Ø
Temperature range (fixed)	-40...+85 °C
Temperature range (mobile)	-25...+85 °C

Technical Data

Operating voltage	max. 30 V AC/DC
Rated surge voltage	0.8 kV
Operating current per contact	max. 1.5 A

No. of poles	12
Material group	IEC 60664-1, category I
Coding	A-coded
LED display	no
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Compression gland	M12 (SW14)
Protection	IP67 inserted and tightened (EN 60529)
Protection NEMA	3, 4, 6P (UL 50E)
Locking material	Brass, nickel plated

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879332262
eClass	27279220
Packaging unit	1

Sketch

1	■	brown
2	■	blue
3	■	white
4	■	green
5	■	pink
6	■	yellow
7	■	black
8	■	gray
9	■	red
10	■	violet
11	■	gray/pink
12	■	red/blue

Product may differ from Image