


M12 female receptacle X coded rear mount solder

Ethernet CAT6A
Flange female
M12, 8-pole
X-coded
shielded
Solder connection
Rear mounting

[**Link to Product**](#)**Illustration**

Product may differ from Image

More Info**Form**

Form 21161

General data

Temperature range -40...+85 °C



Standards DIN EN 61076-2-109 (M12)

Technical Data	
Operating voltage	max. 50 V AC/60 V DC
Operating current per contact	max. 0.5 A
Transfer parameters	CAT6, Class EA (ISO/IEC 11801:2002), (EN 50173-1)
Transfer rate	10 Gbit/s
Coding	M12, X-coded
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Protection	IP67 inserted and tightened (EN 60529)
Housing	Brass, nickel plated

Commercial data	
country of origin	DE
customs tariff number	85366990
EAN	4048879504126
eClass	27279220
Packaging unit	1

Sketch

Female



Product may differ from Image