


M12 MALE 90° / M12 FEMALE 90°

PVC 3X0.34 GRAY, UL/CSA 5m


Male 90° – female 90°  
M12 – M12, 3-pole  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
with cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

Form

Form 40241

Cables

|                            |                  |
|----------------------------|------------------|
| No./diameter of wires      | 3 x 0.34 mm²     |
| Wire isolation             | PVC (br, bl, bk) |
| Material (jacket)          | PVC (UL/CSA)     |
| Outer Ø                    | 4.6 mm ±5%       |
| Bend radius (moving)       | 10× outer Ø      |
| Temperature range (fixed)  | -30...+80 °C     |
| Temperature range (mobile) | -5...+80 °C      |
| Cable identification       | 213              |

|                                     |                                                |
|-------------------------------------|------------------------------------------------|
| Cable Type                          | 1 (PVC)                                        |
| Approval (cable)                    | UL (AWM-Style 2464/1731), CSA                  |
| Cable weight [g/m]                  | 34,10                                          |
| Material (wire)                     | Cu wire, bare                                  |
| Resistor (core)                     | max. 60 $\Omega$ /km (20 °C)                   |
| Single wire $\varnothing$ (core)    | 0.15 mm                                        |
| Construction (core)                 | 19× 0.15 mm (multi-strand wire class 5)        |
| Diameter (core)                     | 3× 0.34 mm <sup>2</sup>                        |
| AWG                                 | similar to AWG 22                              |
| Material (wire isolation)           | PVC                                            |
| Material property (wire isolation)  | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (wire isolation)     | 45 ±5 D                                        |
| Wire- $\varnothing$ incl. isolation | 1.25 mm ±5%                                    |
| Color/numbering of wires            | br, bk, bl                                     |
| Stranding combination               | 3 wires twisted                                |
| Shield                              | no                                             |
| Material (jacket)                   | PVC                                            |
| Material property (jacket)          | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)             | 85 ±5 A                                        |
| Outer- $\varnothing$ (jacket)       | 4.6 mm ±5%                                     |
| Color (jacket)                      | gray                                           |
| chemical resistance                 | good resistance to oil, gasoline and chemicals |
| thermal resistance                  | flame retardant UL 1581 VW1 / CSA FT1          |
| Nominal voltage                     | UL 300 V AC                                    |
| Test voltage                        | 2000 V AC                                      |
| Current load capacity               | to DIN VDE 0298-4                              |
| Temperature range (fixed)           | -30...+80 °C                                   |
| Temperature range (mobile)          | -5...+80 °C                                    |
| Bend radius (fixed)                 | 5× outer $\varnothing$                         |
| Bend radius (moving)                | 10× outer $\varnothing$                        |
| Jacket Color                        | gray                                           |

**Technical Data**




|                                                        |                                                                  |
|--------------------------------------------------------|------------------------------------------------------------------|
| Operating voltage                                      | max. 250 V AC/DC                                                 |
| Operating voltage (only UL listed)                     | max. 30 V AC/DC                                                  |
| Rated surge voltage                                    | 2.5 kV                                                           |
| Operating current per contact                          | max. 4 A                                                         |
| No. of poles                                           | 3                                                                |
| Material group                                         | IEC 60664-1, category I                                          |
| Coding                                                 | A-coded                                                          |
| LED display                                            | no                                                               |
| Locking of ports                                       | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                                      | M12 (SW13)                                                       |
| Protection                                             | IP65, IP66K, IP67 inserted and tightened (EN 60529)              |
| Locking material                                       | Zinc die casting, matte nickel plated                            |
| Material                                               | PUR                                                              |
| suitable for corrugated tube (internal $\varnothing$ ) | 10 mm                                                            |

**General data**

|                  |                          |
|------------------|--------------------------|
| Standards        | DIN EN 61076-2-101 (M12) |
| Mounting method  | inserted, tightened      |
| Pollution Degree | 3                        |

Temperature range -25...+85 °C, depending on cable quality

| Commercial data       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879173407 |
| eClass                | 27279218      |
| Packaging unit        | 1             |
| Sketch                |               |



Product may differ from Image