

**M12 MALE 0° / M12 FEMALE 90° LED**

PUR 5X0.34 GRAY, UL/CSA, ROBOT, drag ch 1.5m

Male straight – female 90°

M12 – M12, 5-pole

3× LED (PNP), (NPN) on request


Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

Zinc die casting, save-cover coated

**Illustration**

Product may differ from Image

**Approvals****Form**

Form 40363

**Cables**

|                                    |                                                   |
|------------------------------------|---------------------------------------------------|
| No./diameter of wires              | 5 × 0.34 mm <sup>2</sup>                          |
| Wire isolation                     | PP (br, wh, bl, bk, gnye)                         |
| C-track properties                 | 10 Mio.                                           |
| Material (jacket)                  | PUR (UL/CSA), welding spark                       |
| Outer Ø                            | 5.0 mm ±5%                                        |
| Bend radius (moving)               | 10 × outer Ø                                      |
| Temperature range (fixed)          | -40...+80 °C                                      |
| Temperature range (mobile)         | -25...+80 °C                                      |
| Cable identification               | 255                                               |
| Cable Type                         | 5 (PUR schweißfunkenbeständig)                    |
| Approval (cable)                   | cURus (AWM-Style 20549/10493); CE conform         |
| Cable weight [g/m]                 | 41,80                                             |
| Material (wire)                    | Cu wire, bare                                     |
| Resistor (core)                    | max. 60 Ω/km (20 °C)                              |
| Single wire Ø (core)               | 0.1 mm                                            |
| Construction (core)                | 42 × 0.1 mm (multi-strand wire class 6)           |
| Diameter (core)                    | 5 × 0.34 mm <sup>2</sup>                          |
| AWG                                | similar to AWG 22                                 |
| Material (wire isolation)          | PP                                                |
| Material property (wire isolation) | CFC-, halogen-, cadmium-, silicone- and lead-free |
| Shore hardness (wire isolation)    | 74 ±3 D                                           |

|                                 |                                                                                                                                                                         |
|---------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire-Ø incl. isolation          | 1.25 mm ±5%                                                                                                                                                             |
| Color/numbering of wires        | br, bk, bl, wh, gnye longitudinally striped                                                                                                                             |
| Shield                          | no                                                                                                                                                                      |
| Stranding combination           | 5 wires twisted around central filler                                                                                                                                   |
| Material (jacket)               | PUR                                                                                                                                                                     |
| Material property (jacket)      | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis-, microbial- and welding spark resistant |
| Shore hardness (jacket)         | 58 ±3 D                                                                                                                                                                 |
| Outer-Ø (jacket)                | 5.0 mm ±5%                                                                                                                                                              |
| Color (jacket)                  | gray                                                                                                                                                                    |
| chemical resistance             | good resistance to oil, gasoline and chemicals (EN 60811-404)                                                                                                           |
| thermal resistance              | flame retardant UL, FT2, IEC 60332-1, IEC 60332-2-2, welding spark resistant                                                                                            |
| Nominal voltage                 | 300 V AC                                                                                                                                                                |
| Test voltage                    | 2500 V AC                                                                                                                                                               |
| Current load capacity           | to DIN VDE 0298-4                                                                                                                                                       |
| Temperature range (fixed)       | -40...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                                   |
| Temperature range (mobile)      | -25...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                                   |
| Bend radius (fixed)             | 5× outer Ø                                                                                                                                                              |
| Bend radius (moving)            | 10× outer Ø                                                                                                                                                             |
| No. of bending cycles (C-track) | max. 10 Mio. (25 °C)                                                                                                                                                    |
| Traversing distance (C-track)   | max. 5 m (horizontal)                                                                                                                                                   |
| Travel speed (C-track)          | max. 3.3 m/s                                                                                                                                                            |
| Acceleration (C-track)          | min. 5 m/s²                                                                                                                                                             |
| Torsion stress                  | ±360°/m                                                                                                                                                                 |
| No. of torsion cycles           | max. 1 Mio. (25 °C)                                                                                                                                                     |
| Torsion speed                   | 35 cycles/min                                                                                                                                                           |
| Jacket Color                    | gray                                                                                                                                                                    |

**Technical Data**

|                                           |                                                                  |
|-------------------------------------------|------------------------------------------------------------------|
| Operating voltage                         | 24 V DC ±25%                                                     |
| Rated surge voltage                       | 0.8 kV                                                           |
| Operating current per contact             | max. 4 A                                                         |
| No. of poles                              | 5                                                                |
| Material group                            | IEC 60664-1, category I                                          |
| Coding                                    | A-coded                                                          |
| LED display                               | green, yellow, red                                               |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                         | M12 (SW13)                                                       |
| Protection                                | IP65 and IP67 when plugged and screwed down (EN 60529)           |
| Material                                  | PUR                                                              |
| suitable for corrugated tube (internal Ø) | 10 mm                                                            |
| Locking material                          | Zinc die casting, save-cover coated                              |

**General data**


|                   |                                          |
|-------------------|------------------------------------------|
| Pollution Degree  | 3                                        |
| Mounting method   | inserted, tightened                      |
| Temperature range | -25...+85 °C, depending on cable quality |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879445221 |
| eClass                | 27279218      |

Packaging unit 1

Sketch



Product may differ from Image