


M12 male 90° / M12 female 90° LED

PUR 5x0.34 bk UL/CSA 3m


Male 90° – female 90°  
M12 – M12, 5-pole  
3× LED (PNP), (NPN) on request  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

Form

Form 40441

Cables

|                           |                            |
|---------------------------|----------------------------|
| No./diameter of wires     | 5× 0.34 mm <sup>2</sup>    |
| Wire isolation            | PVC (br, wh, bl, bk, gnye) |
| C-track properties        | 2 Mio.                     |
| Material (jacket)         | PUR/PVC (UL/CSA)           |
| Outer Ø                   | 5.9 mm ±5%                 |
| Bend radius (moving)      | 15× outer Ø                |
| Temperature range (fixed) | -30...+80 °C               |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Cable identification               | 625                                                                                                                                                    |
| Cable Type                         | 2 (PUR/PVC)                                                                                                                                            |
| Approval (cable)                   | UL (AWM-Style 20549/1731), CSA; CE conform                                                                                                             |
| Cable weight [g/m]                 | 54,78                                                                                                                                                  |
| Material (wire)                    | Cu wire, bare                                                                                                                                          |
| Resistor (core)                    | max. 57 $\Omega$ /km (20 °C)                                                                                                                           |
| Single wire Ø (core)               | 0.1 mm                                                                                                                                                 |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                    | 5× 0.34 mm²                                                                                                                                            |
| AWG                                | similar to AWG 22                                                                                                                                      |
| Material (wire isolation)          | PVC                                                                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness (wire isolation)    | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped                                                                                                            |
| Stranding combination              | 5 wires twisted around central filler                                                                                                                  |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR/PVC                                                                                                                                                |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                   | 5.9 mm ±5%                                                                                                                                             |
| Color (jacket)                     | black                                                                                                                                                  |
| chemical resistance                | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                    | UL 300 V AC                                                                                                                                            |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)                | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s²                                                                                                                                            |
| Jacket Color                       | black                                                                                                                                                  |

#### Technical Data

|                                           |                                                                    |
|-------------------------------------------|--------------------------------------------------------------------|
| Operating voltage                         | 24 V DC ±25%                                                       |
| Operating voltage (only UL listed)        | max. 30 V DC                                                       |
| Operating current per contact             | max. 4 A                                                           |
| Material group                            | IEC 60664-1, category I                                            |
| Coding                                    | A-coded                                                            |
| LED display                               | LED (green): Power / LED (yellow): (S1) / LED (white): Signal (S2) |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing   |
| Compression gland                         | M12 (SW13)                                                         |
| Protection                                | IP66K, IP67 inserted and tightened (EN 60529)                      |
| Locking material                          | Zinc die casting, matte nickel plated                              |
| Material                                  | PUR                                                                |
| suitable for corrugated tube (internal Ø) | 10 mm                                                              |



General data

|                   |                                          |
|-------------------|------------------------------------------|
| Pollution Degree  | 3                                        |
| Temperature range | -25...+85 °C, depending on cable quality |


Commercial data

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879166409 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

Sketch



(\* for cable type 126, 732, 219, 619)



Product may differ from Image