

M12 male 0° / M12 female 0° shielded

PUR 5x0.34 shielded bk UL/CSA+drag chain 0,6m

Male straight – female straight

M12 – M12, 5-pole

A-coded


shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

Illustration



Product may differ from Image

Approvals

cCSAus



\* only for products with UL/CSA approved cable

EAC

Form

Form 40521

Cables

|                       |                           |
|-----------------------|---------------------------|
| No./diameter of wires | 5 x 0.34 mm <sup>2</sup>  |
| Wire isolation        | PP (br, wh, bl, bk, gnye) |
| C-track properties    | 5 Mio.                    |
| Material (jacket)     | PUR (UL/CSA)              |
| Outer Ø               | 5.6 mm ±5%                |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Bend radius (moving)               | 10× outer Ø                                                                                                                                            |
| Temperature range (fixed)          | -40...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -25...+80 °C                                                                                                                                           |
| Cable identification               | 642                                                                                                                                                    |
| Cable Type                         | 3 (PUR)                                                                                                                                                |
| Approval (cable)                   | cURus (AWM-Style 20549/10493); CE conform                                                                                                              |
| Cable weight [g/m]                 | 57,20                                                                                                                                                  |
| Material (wire)                    | Cu wire, bare                                                                                                                                          |
| Resistor (core)                    | max. 57 Ω/km (20 °C)                                                                                                                                   |
| Single wire Ø (core)               | 0.1 mm                                                                                                                                                 |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                    | 5× 0.34 mm²                                                                                                                                            |
| AWG                                | similar to AWG 22                                                                                                                                      |
| Material (wire isolation)          | PP                                                                                                                                                     |
| Material property (wire isolation) | CFC-, halogen-, cadmium-, silicone- and lead-free                                                                                                      |
| Shore hardness (wire isolation)    | 70 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped                                                                                                            |
| Stranding combination              | 5 wires twisted around central filler                                                                                                                  |
| Shield                             | yes                                                                                                                                                    |
|                                    | min. 80%                                                                                                                                               |
| Material (jacket)                  | PUR                                                                                                                                                    |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 90 ±5 A                                                                                                                                                |
| Outer-Ø (jacket)                   | 5.6 mm ±5%                                                                                                                                             |
| Color (jacket)                     | black                                                                                                                                                  |
| chemical resistance                | good resistance to oil, gasoline and chemicals (EN 60811-404)                                                                                          |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2                                                                                     |
| Nominal voltage                    | 300 V AC                                                                                                                                               |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -40...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                  |
| Temperature range (mobile)         | -25...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                  |
| Bend radius (fixed)                | 5× outer Ø                                                                                                                                             |
| Bend radius (moving)               | 10× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 5 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s²                                                                                                                                            |
| Torsion stress                     | ±30 °/m                                                                                                                                                |
| No. of torsion cycles              | max. 2 Mio. (25 °C)                                                                                                                                    |
| Torsion speed                      | 35 cycles/min                                                                                                                                          |
| Jacket Color                       | black                                                                                                                                                  |
| <b>Technical Data</b>              |                                                                                                                                                        |
| Operating voltage                  | max. 60 V AC/DC                                                                                                                                        |
| Operating voltage (only UL listed) | 30 V AC/DC                                                                                                                                             |
| Rated surge voltage                | 1.5 kV                                                                                                                                                 |
| Operating current per contact      | max. 4 A                                                                                                                                               |
| No. of poles                       | 5                                                                                                                                                      |

|                                           |                                                                  |
|-------------------------------------------|------------------------------------------------------------------|
| Material group                            | IEC 60664-1, category I                                          |
| Coding                                    | A-coded                                                          |
| LED display                               | no                                                               |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                         | M12 (SW13)                                                       |
| Protection                                | IP65 and IP67 when plugged and screwed down (EN 60529)           |
| Locking material                          | Zinc die casting, matte nickel plated                            |
| Material                                  | PUR                                                              |
| suitable for corrugated tube (internal Ø) | without                                                          |


General data

|                            |                                          |
|----------------------------|------------------------------------------|
| Standards                  | DIN EN 61076-2-101 (M12)                 |
| Mounting method            | inserted, tightened                      |
| Material (contact)         | Copper alloy                             |
| Material (contact surface) | Au                                       |
| Material (gasket)          | FKM                                      |
| Pollution Degree           | 3                                        |
| Temperature range          | -25...+85 °C, depending on cable quality |


Commercial data

|                       |               |
|-----------------------|---------------|
| country of origin     | CZ            |
| customs tariff number | 85444290      |
| EAN                   | 4048879473927 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

Sketch



(\* for cable type 203, 603, 243, 643)



Product may differ from Image