

M12 male 0° / M8 female 0°

PUR 3x0.25 ye UL/CSA 0,6m

Male straight – female straight

M12 – M8, 3-pole

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request


Art-No. 7005 - M8 Lite - (plastic hexagonal screw) on request

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

Illustration



Product may differ from Image

Approvals



cCSAus

\* only for products with UL/CSA approved cable

Form

Form 40561

Cables

|                            |                                            |
|----------------------------|--------------------------------------------|
| No./diameter of wires      | 3 × 0.25 mm <sup>2</sup>                   |
| Wire isolation             | PVC (br, bl, bk)                           |
| C-track properties         | 2 Mio.                                     |
| Material (jacket)          | PUR/PVC (UL/CSA)                           |
| Outer Ø                    | 4.5 mm ±5%                                 |
| Temperature range (fixed)  | -30...+80 °C                               |
| Temperature range (mobile) | -5...+80 °C                                |
| Bend radius (moving)       | 15× outer Ø                                |
| Cable identification       | 020                                        |
| Cable Type                 | 2 (PUR/PVC)                                |
| Approval (cable)           | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]         | 26,62                                      |
| Material (wire)            | Cu wire, bare                              |
| Resistor (core)            | max. 79 Ω/km (20 °C)                       |
| Single wire Ø (core)       | 0.1 mm                                     |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Construction (core)                | 32× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                    | 3× 0.25 mm <sup>2</sup>                                                                                                                                |
| AWG                                | similar to AWG 24                                                                                                                                      |
| Material (wire isolation)          | PVC                                                                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness (wire isolation)    | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl                                                                                                                                             |
| Stranding combination              | 3 wires twisted                                                                                                                                        |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR                                                                                                                                                    |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 85 ±5 A                                                                                                                                                |
| Outer-Ø (jacket)                   | 4.5 mm ±5%                                                                                                                                             |
| Color (jacket)                     | yellow                                                                                                                                                 |
| chemical resistance                | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                    | UL 300 V AC                                                                                                                                            |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)                | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s <sup>2</sup>                                                                                                                                |
| Jacket Color                       | yellow                                                                                                                                                 |

#### Technical Data

|                                           |                                                                         |
|-------------------------------------------|-------------------------------------------------------------------------|
| Operating voltage                         | max. 50 V AC/60 V DC                                                    |
| Operating voltage (only UL listed)        | max. 30 V AC/DC                                                         |
| Rated surge voltage                       | 1.5 kV                                                                  |
| Operating current per contact             | max. 4 A                                                                |
| Material group                            | IEC 60664-1, category I                                                 |
| Coding                                    | A-coded                                                                 |
| Locking of ports                          | Screw thread (M8/M12×1 mm) recommended torque 0.4/0.6 Nm, self-securing |
| Compression gland                         | M8 (SW9), M12 (SW13)                                                    |
| Protection                                | IP65, IP66K, IP67 inserted and tightened (EN 60529)                     |
| Locking material                          | Zinc die casting, matte nickel plated                                   |
| Material                                  | PUR                                                                     |
| suitable for corrugated tube (internal Ø) | M12 (10 mm); M8 (6.5 mm)                                                |

#### General data


|                   |                                                   |
|-------------------|---------------------------------------------------|
| Standards         | DIN EN 61076-2-101 (M12), DIN EN 61076-2-104 (M8) |
| Mounting method   | inserted, tightened                               |
| Pollution Degree  | 3                                                 |
| Material (gasket) | FKM                                               |
| Temperature range | -25...+85 °C, depending on cable quality          |

#### Commercial data

|                   |    |
|-------------------|----|
| country of origin | DE |
|-------------------|----|


|                       |               |
|-----------------------|---------------|
| customs tariff number | 85444290      |
| EAN                   | 4048879164313 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

Sketch



Male

Female



Product may differ from Image