


**M12 Y-distributor / M12 female 0°**

PUR 5x0.34 gy UL/CSA 0,3m

Y-connector M12 – M12, 5-pole  
Male straight – females straight  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 40725

General data

|                            |                                          |
|----------------------------|------------------------------------------|
| Material (contact)         | Copper alloy                             |
| Material (contact surface) | Au                                       |
| Material (gasket)          | FKM                                      |
| Pollution Degree           | 3                                        |
| Temperature range          | -25...+85 °C, depending on cable quality |

Cables

|                       |                            |
|-----------------------|----------------------------|
| No./diameter of wires | 5× 0.34 mm²                |
| Wire isolation        | PVC (br, wh, bl, bk, gnye) |
| C-track properties    | 2 Mio.                     |
| Material (jacket)     | PUR/PVC (UL/CSA)           |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Outer Ø                            | 5.9 mm ±5%                                                                                                                                             |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Cable identification               | 225                                                                                                                                                    |
| Cable Type                         | 2 (PUR/PVC)                                                                                                                                            |
| Approval (cable)                   | UL (AWM-Style 20549/1731), CSA; CE conform                                                                                                             |
| Cable weight [g/m]                 | 54,78                                                                                                                                                  |
| Material (wire)                    | Cu wire, bare                                                                                                                                          |
| Resistor (core)                    | max. 57 Ω/km (20 °C)                                                                                                                                   |
| Single wire Ø (core)               | 0.1 mm                                                                                                                                                 |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                    | 5× 0.34 mm <sup>2</sup>                                                                                                                                |
| AWG                                | similar to AWG 22                                                                                                                                      |
| Material (wire isolation)          | PVC                                                                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness (wire isolation)    | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped                                                                                                            |
| Stranding combination              | 5 wires twisted around central filler                                                                                                                  |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR/PVC                                                                                                                                                |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                   | 5.9 mm ±5%                                                                                                                                             |
| Color (jacket)                     | gray                                                                                                                                                   |
| chemical resistance                | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                    | UL 300 V AC                                                                                                                                            |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)                | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s <sup>2</sup>                                                                                                                                |
| Jacket Color                       | gray                                                                                                                                                   |

#### Technical Data




|                               |                                                                  |
|-------------------------------|------------------------------------------------------------------|
| Operating voltage             | max. 125 V AC/DC                                                 |
| Rated surge voltage           | 1.5 kV                                                           |
| Operating current per contact | max. 4 A                                                         |
| No. of poles                  | 5-pole                                                           |
| Material group                | IEC 60664-1, category I                                          |
| Coding                        | A-coded                                                          |
| LED display                   | no                                                               |
| Locking of ports              | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |

|                                           |                                                        |
|-------------------------------------------|--------------------------------------------------------|
| Compression gland                         | M12 (SW13)                                             |
| Protection                                | IP65 and IP67 when plugged and screwed down (EN 60529) |
| Locking material                          | Zinc die casting, matte nickel plated                  |
| Material                                  | PUR                                                    |
| suitable for corrugated tube (internal Ø) | 10 mm                                                  |

Commercial data

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879587792 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

Sketch



Product may differ from Image