

**M12 MALE 90° / MSUD VALVE PLUG FORM A 18MM**

PVC 5X0.34 GRAY, 1.5m

**MSUD**

Form A (18 mm) – M12, male 90°

24 V DC  $\pm 25\%$ 


LED (red/green)

for pressure switches


Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.



**Illustration**

Height: 30 mm



Female

Male




Product may differ from Image

**Approvals**



| Cables                             |                                                |
|------------------------------------|------------------------------------------------|
| No./diameter of wires              | 5× 0.34 mm <sup>2</sup>                        |
| Wire isolation                     | PVC (br, wh, bl, bk, gnye)                     |
| Material (jacket)                  | PVC (UL/CSA)                                   |
| Outer Ø                            | 5.2 mm ±5%                                     |
| Bend radius (moving)               | 10× outer Ø                                    |
| Temperature range (fixed)          | -30...+80 °C                                   |
| Temperature range (mobile)         | -5...+80 °C                                    |
| Cable identification               | 215                                            |
| Cable Type                         | 1 (PVC)                                        |
| Approval (cable)                   | UL (AWM-Style 2464/1731), CSA                  |
| Cable weight [g/m]                 | 48,40                                          |
| Material (wire)                    | Cu wire, bare                                  |
| Resistor (core)                    | max. 60 Ω/km (20 °C)                           |
| Single wire Ø (core)               | 0.15 mm                                        |
| Construction (core)                | 19× 0.15 mm (multi-strand wire class 5)        |
| Diameter (core)                    | 5× 0.34 mm <sup>2</sup>                        |
| AWG                                | similar to AWG 22                              |
| Material (wire isolation)          | PVC                                            |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (wire isolation)    | 45 ±5 D                                        |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                    |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped    |
| Stranding combination              | 5 wires twisted around central filler          |
| Shield                             | no                                             |
| Material (jacket)                  | PVC                                            |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)            | 85 ±5 A                                        |
| Outer-Ø (jacket)                   | 5.2 mm ±5%                                     |
| Color (jacket)                     | gray                                           |
| chemical resistance                | good resistance to oil, gasoline and chemicals |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1          |
| Nominal voltage                    | UL 300 V AC                                    |
| Test voltage                       | 2000 V AC                                      |
| Current load capacity              | to DIN VDE 0298-4                              |
| Temperature range (fixed)          | -30...+80 °C                                   |
| Temperature range (mobile)         | -5...+80 °C                                    |
| Bend radius (fixed)                | 5× outer Ø                                     |
| Bend radius (moving)               | 10× outer Ø                                    |
| Jacket Color                       | gray                                           |
| Technical Data                     |                                                |
| Operating voltage                  | 24 V DC ±25%                                   |
| Operating current per contact      | max. 4 A                                       |
| Current consumption                | approx. 12 mA                                  |
| Housing                            | Black plastic (gray on request)                |
| Locking of ports                   | M3/M12×1 mm (recommended torque 0.4/0.6 Nm)    |

|                       |                                               |
|-----------------------|-----------------------------------------------|
| Protection            | IP66K, IP67 inserted and tightened (EN 60529) |
| Rated surge voltage   | 0.8 kV                                        |
| General data          |                                               |
| Temperature range     | -25...+85 °C, depending on cable quality      |
| Commercial data       |                                               |
| country of origin     | CZ                                            |
| customs tariff number | 85444290                                      |
| EAN                   | 4048879447829                                 |
| eClass                | 27279218                                      |
| Packaging unit        | 1                                             |
| Sketch                |                                               |



Product may differ from Image