

M12 MALE 90° / MSUD VALVE PLUG FORM B 10 MM

PUR 3X0.75 GRAY, 0.3m

Form B (10 mm) – M12, male 90°

24 V AC ±20% / DC ±25%



LED and suppression

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Illustration



Product may differ from Image

Approvals



Form

Form 41021

Cables

|                            |                                            |
|----------------------------|--------------------------------------------|
| No./diameter of wires      | 3× 0.75 mm²                                |
| Wire isolation             | PVC (bk num, gnye)                         |
| C-track properties         | 2 Mio.                                     |
| Material (jacket)          | PUR/PVC (UL/CSA)                           |
| Outer Ø                    | 5.9 mm ±5%                                 |
| Bend radius (moving)       | 15× outer Ø                                |
| Temperature range (fixed)  | -30...+80 °C                               |
| Temperature range (mobile) | -5...+80 °C                                |
| Cable identification       | 226                                        |
| Cable Type                 | 2 (PUR/PVC)                                |
| Approval (cable)           | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]         | 55,33                                      |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material (wire)                    | Cu wire, bare                                                                                                                                          |
| Resistor (core)                    | max. 26 $\Omega$ /km (20 °C)                                                                                                                           |
| Single wire Ø (core)               | 0.15 mm                                                                                                                                                |
| Construction (core)                | 42× 0.15 mm (multi-strand wire class 6)                                                                                                                |
| Diameter (core)                    | 3× 0.75 mm <sup>2</sup>                                                                                                                                |
| AWG                                | similar to AWG 18                                                                                                                                      |
| Material (wire isolation)          | PVC                                                                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness (wire isolation)    | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.8 mm ±5%                                                                                                                                             |
| Color/numbering of wires           | bk numbered, gnye longitudinally striped                                                                                                               |
| Stranding combination              | 3 wires twisted                                                                                                                                        |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR/PVC                                                                                                                                                |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                   | 5.9 mm ±5%                                                                                                                                             |
| Color (jacket)                     | gray                                                                                                                                                   |
| chemical resistance                | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                    | UL 300 V AC                                                                                                                                            |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)                | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s <sup>2</sup>                                                                                                                                |
| Jacket Color                       | gray                                                                                                                                                   |

**Technical Data**

|                               |                                               |
|-------------------------------|-----------------------------------------------|
| Operating voltage             | 24 V AC ±20% / DC ±25%                        |
| Operating current per contact | max. 4 A                                      |
| Switch off peak               | max. 55 V                                     |
| Switch off delay time         | max. 20 ms                                    |
| LED display                   | (yellow)                                      |
| Current consumption           | approx. 12 mA                                 |
| Housing                       | Black plastic (gray on request)               |
| Locking of ports              | M3/M12×1 mm (recommended torque 0.4/0.6 Nm)   |
| Protection                    | IP66K, IP67 inserted and tightened (EN 60529) |
| Rated surge voltage           | 0.8 kV                                        |

**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Temperature range | -25...+85 °C, depending on cable quality |
|-------------------|------------------------------------------|

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | CZ            |
| customs tariff number | 85444290      |
| EAN                   | 4048879147347 |
| eClass                | 27279218      |

Packaging unit

1