

**M12 male 0°/M12 female 0° shielded B-cod.Profibus**

PUR 1x2xAWG22 shielded vt UL/CSA+drag chain 1m

**PROFIBUS**

Male straight – female straight

M12, 4-pole – M12, 2-pole




B-coded

shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Illustration**

Product may differ from Image

## Approvals

cCSAus



\* only for products with UL/CSA approved cable

## More Info



## Form

Form 44001

## Cables

|                            |                                         |
|----------------------------|-----------------------------------------|
| Cable number               | 786                                     |
| No./diameter of wires      | 1 × 2 × AWG22                           |
| Wire isolation             | PE (rd, gn)                             |
| C-track properties         | 2 Mio.                                  |
| Jacket Color               | violet                                  |
| Material (jacket)          | PUR (UL/CSA)                            |
| Outer Ø                    | 8.1 mm ±5%                              |
| Bend radius (moving)       | 12× outer Ø                             |
| Temperature range (fixed)  | -40...+80 °C                            |
| Temperature range (mobile) | -20...+60 °C                            |
| Cable identification       | 786                                     |
| Approval (cable)           | UL (AWM-Style 20233/10578), CSA; CE     |
| Cable weight [g/m]         | 81,40                                   |
| Material (wire)            | Cu wire, bare                           |
| Resistor (core)            | max. 55 Ω/km (20 °C)                    |
| Single wire Ø (core)       | 0.16 mm                                 |
| Construction (core)        | 19× 0.16 mm (multi-strand wire class 5) |
| Diameter (core)            | 1 × 2 × AWG22                           |
| Material (wire isolation)  | PE                                      |
| Wire-Ø incl. isolation     | 2.85 mm ±5%                             |
| Color/numbering of wires   | rd, gn                                  |
| Shield                     | yes                                     |
|                            | min. 85%                                |
| Material (jacket)          | PUR                                     |
| Outer-Ø (jacket)           | 8.1 mm ±5%                              |
| Color (jacket)             | violet                                  |
| Nominal voltage            | 300 V                                   |
| Temperature range (fixed)  | -40...+80 °C                            |
| Temperature range (mobile) | -20...+60 °C                            |
| Bend radius (fixed)        | 6× outer Ø                              |
| Bend radius (moving)       | 12× outer Ø                             |
| Travel speed (C-track)     | max. 3 m/s                              |
| Acceleration (C-track)     | max. 3 m/s²                             |

## Technical Data

Operating voltage max. 60 V AC/DC

|                                           |                                                                  |
|-------------------------------------------|------------------------------------------------------------------|
| Operating voltage (only UL listed)        | max. 30 V AC/DC                                                  |
| Rated surge voltage                       | 1.5 kV                                                           |
| Operating current per contact             | max. 4 A                                                         |
| Material group                            | IEC 60664-1, category I                                          |
| Coding                                    | B-coded                                                          |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                         | M12 (SW13)                                                       |
| Protection                                | IP65, IP66K, IP67 inserted and tightened (EN 60529)              |
| Locking material                          | Zinc die casting, matte nickel plated                            |
| Material                                  | PUR                                                              |
| suitable for corrugated tube (internal Ø) | without                                                          |

**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Standards         | DIN EN 61076-2-101 (M12)                 |
| Mounting method   | inserted, tightened                      |
| Pollution Degree  | 3                                        |
| Temperature range | -25...+85 °C, depending on cable quality |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879629478 |
| eClass                | 27061801      |
| Packaging unit        | 1             |