

**M12 male 90°/M12 female 0° shielded B-cod.Profibus**

PUR 1x2xAWG24 shielded vt UL/CSA+dragchain 0.2m

PROFIBUS

Male 90° – female straight

M12 – M12, 2-pole

B-coded




shielded

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Illustration**



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

More Info

**Form**

Form 44041

**Cables**

|                                    |                                                                                                          |
|------------------------------------|----------------------------------------------------------------------------------------------------------|
| No./diameter of wires              | 1 × 2 × 0.25 mm <sup>2</sup>                                                                             |
| Wire isolation                     | PE (rd, gn)                                                                                              |
| C-track properties                 | 5 Mio.                                                                                                   |
| Material (jacket)                  | PUR (UL/CSA)                                                                                             |
| Outer Ø                            | 7.7 mm ±5%                                                                                               |
| Bend radius (moving)               | 12× outer Ø                                                                                              |
| Temperature range (fixed)          | -40...+80 °C                                                                                             |
| Temperature range (mobile)         | -20...+60 °C                                                                                             |
| Cable identification               | 841                                                                                                      |
| Approval (cable)                   | UL (AWM-Style 20233), CE-conform                                                                         |
| Cable weight [g/m]                 | 70,40                                                                                                    |
| Material (wire)                    | Cu wire, bare                                                                                            |
| Resistor (core)                    | max. 72 Ω/km (20 °C)                                                                                     |
| Single wire Ø (core)               | 0.13 mm                                                                                                  |
| Construction (core)                | 19 × 0.13 mm                                                                                             |
| Diameter (core)                    | 1 × 2 × 0.25 mm <sup>2</sup>                                                                             |
| AWG                                | similar to AWG 24                                                                                        |
| Material (wire isolation)          | ZE-PE                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                  |
| Shore hardness (wire isolation)    | 60 ±3 D                                                                                                  |
| Wire-Ø incl. isolation             | 2.55 mm ±5%                                                                                              |
| Color/numbering of wires           | rd, gn                                                                                                   |
| Shield                             | yes                                                                                                      |
|                                    | min. 85%                                                                                                 |
| Material (jacket)                  | PUR                                                                                                      |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant |
| Shore hardness (jacket)            | 87 ±3 A                                                                                                  |
| Outer-Ø (jacket)                   | 7.7 mm ±5%                                                                                               |
| Color (jacket)                     | violet                                                                                                   |
| chemical resistance                | good resistance to oil, gasoline and chemicals (VDE 0472 Teil 803 Test B)                                |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1                                                                    |
| Nominal voltage                    | 300 V                                                                                                    |
| Test voltage                       | 1500 V AC                                                                                                |
| Temperature range (fixed)          | -40...+80 °C                                                                                             |
| Temperature range (mobile)         | -20...+60 °C                                                                                             |
| Bend radius (fixed)                | 7.5× outer Ø                                                                                             |
| Bend radius (moving)               | 12× outer Ø                                                                                              |
| No. of bending cycles (C-track)    | max. 5 Mio. (25 °C)                                                                                      |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                    |
| Travel speed (C-track)             | max. 3 m/s                                                                                               |
| Acceleration (C-track)             | max. 5 m/s <sup>2</sup>                                                                                  |
| Jacket Color                       | violet                                                                                                   |

**Technical Data**

|                                    |                                                                  |
|------------------------------------|------------------------------------------------------------------|
| Operating voltage                  | max. 60 V AC/DC                                                  |
| Operating voltage (only UL listed) | max. 30 V AC/DC                                                  |
| Operating current per contact      | max. 4 A                                                         |
| Locking of ports                   | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Locking material                   | Zinc die casting, matte nickel plated                            |
| Protection                         | IP66K, IP67 inserted and tightened (EN 60529)                    |
| Rated surge voltage                | 1.5 kV                                                           |
| <b>Commercial data</b>             |                                                                  |
| country of origin                  | DE                                                               |
| customs tariff number              | 85444290                                                         |
| EAN                                | 4048879379861                                                    |
| eClass                             | 27061801                                                         |
| Packaging unit                     | 1                                                                |