


M12 male 0° / M12 male, 0°, shielded, Ethernet

PUR 1x4xAWG26 shielded gn UL,CSA+drag chain 2,5m


Ethernet CAT5e  
Male straight – male straight  
M12 – M12, 4-pole  
D-coded  
shielded  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Transmission properties with channel transmission up to 50 m

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

cCSAus

More Info

EtherNet/IP

EtherCAT

PROFIBUS

Form

Form 44511

Cables

|                       |                              |
|-----------------------|------------------------------|
| No./diameter of wires | 1 × 4 × 0.15 mm <sup>2</sup> |
| Wire isolation        | PO (wh, ye, bl, or)          |
| C-track properties    | 5 Mio.                       |
| Material (jacket)     | PUR (UL/CSA)                 |

|                                 |                                                   |
|---------------------------------|---------------------------------------------------|
| Outer Ø                         | 4.9 mm ±5%                                        |
| Bend radius (moving)            | 12× outer Ø                                       |
| Temperature range (fixed)       | -20...+80 °C                                      |
| Temperature range (mobile)      | -20...+50 °C                                      |
| Cable identification            | 791                                               |
| Approval (cable)                | UL (AWM-Style 20236/1589), CSA; CE                |
| Cable weight [g/m]              | 59,40                                             |
| Material (wire)                 | Cu wire, bare                                     |
| Resistor (core)                 | max. 139.3 Ω/km (20 °C)                           |
| Single wire Ø (core)            | 0.15 mm                                           |
| Construction (core)             | 19× 0.15 mm (multi-strand wire class 5)           |
| Diameter (core)                 | 1 × 4× AWG26                                      |
| AWG                             | similar to AWG 26                                 |
| Material (wire isolation)       | PO                                                |
| Wire-Ø incl. isolation          | 1.0 mm ±5%                                        |
| Color/numbering of wires        | wh, or, bl, ye                                    |
| Stranding combination           | 4 wires twisted                                   |
| Shield                          | yes                                               |
|                                 | min. 85%                                          |
| Material (jacket)               | PUR                                               |
| Material property (jacket)      | CFC-, halogen-, cadmium-, silicone- and lead-free |
| Outer-Ø (jacket)                | 4.9 mm ±5%                                        |
| Color (jacket)                  | green                                             |
| chemical resistance             | good resistance to oil, gasoline and chemicals    |
| thermal resistance              | flame retardant                                   |
| Temperature range (fixed)       | -20...+80 °C                                      |
| Temperature range (mobile)      | -20...+50 °C                                      |
| Bend radius (fixed)             | 7.5× outer Ø                                      |
| Bend radius (moving)            | 12× outer Ø                                       |
| No. of bending cycles (C-track) | max. 5 Mio. (25 °C)                               |
| Traversing distance (C-track)   | max. 5 m (horizontal)                             |
| Travel speed (C-track)          | max. 300 m/min                                    |
| Acceleration (C-track)          | max. 5 m/s²                                       |
| Jacket Color                    | green                                             |

**Technical Data**

|                                           |                                                                  |
|-------------------------------------------|------------------------------------------------------------------|
| Operating voltage                         | max. 60 V DC                                                     |
| Operating voltage (only UL listed)        | max. 30 V DC                                                     |
| Rated surge voltage                       | 1.5 kV                                                           |
| Operating current per contact             | max. 4 A                                                         |
| Material group                            | IEC 60664-1, category I                                          |
| Transfer parameters                       | CAT5e, Class D (ISO/IEC 11801:2002), (EN 50173-1)                |
| Transfer rate                             | up to 100 Mbit/s full duplex                                     |
| Coding                                    | D-coded                                                          |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                         | M12 (SW13)                                                       |
| Protection                                | IP65, IP66K, IP67 inserted and tightened (EN 60529)              |
| Locking material                          | Zinc die casting, matte nickel plated                            |
| Material                                  | PUR                                                              |
| suitable for corrugated tube (internal Ø) | without                                                          |


**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Standards         | DIN EN 61076-2-101 (M12)                 |
| Pollution Degree  | 3                                        |
| Mounting method   | inserted, tightened                      |
| Temperature range | -25...+85 °C, depending on cable quality |

Commercial data

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879684545 |
| eClass                | 27061801      |
| Packaging unit        | 1             |

Sketch



Male

Male



Product may differ from Image