

**RJ45 Push Pull male 0° / RJ45 male 0° Ethernet**

PUR 2x2xAWG22 shielded gn UL/CSA+dragchain 35m

Ethernet CAT5  
Male straight – male straight  
RJ45 – RJ45PP, 4-pole  
shielded  
Push Pull  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

More Info

EtherNet/IP





Form

Form 74305

General data

|                   |                                          |
|-------------------|------------------------------------------|
| Mounting method   | inserted                                 |
| Pollution Degree  | 3                                        |
| Temperature range | -25...+85 °C, depending on cable quality |

Cables

|                            |                            |
|----------------------------|----------------------------|
| No./diameter of wires      | 2× 2× 0.34 mm <sup>2</sup> |
| Wire isolation             | PE (wh, ye, bl, or)        |
| C-track properties         | 3 Mio.                     |
| Jacket Color               | green                      |
| Material (jacket)          | PUR (UL/CSA)               |
| Outer Ø                    | 6.7 mm ±5%                 |
| Bend radius (moving)       | 12× outer Ø                |
| Temperature range (fixed)  | -40...+80 °C               |
| Temperature range (mobile) | -30...+70 °C               |
| Cable identification       | 796                        |

|                                 |                                                                                                              |
|---------------------------------|--------------------------------------------------------------------------------------------------------------|
| Approval (cable)                | UL (AWM-Style 20233/11602), CSA; CE                                                                          |
| Cable weight [g/m]              | 69,3                                                                                                         |
| Material (wire)                 | Cu wire, bare                                                                                                |
| Resistor (core)                 | max. 55 $\Omega$ /km (20 °C)                                                                                 |
| Diameter (core)                 | 2× 2× AWG22                                                                                                  |
| Material (wire isolation)       | PE                                                                                                           |
| Wire-Ø incl. isolation          | 1.4 mm $\pm$ 5%                                                                                              |
| Color/numbering of wires        | wh, ye, bl, or                                                                                               |
| Shield                          | yes                                                                                                          |
|                                 | min. 85%                                                                                                     |
| Material (jacket)               | PUR                                                                                                          |
| Outer-Ø (jacket)                | 6.7 mm $\pm$ 5%                                                                                              |
| Color (jacket)                  | green                                                                                                        |
| thermal resistance              | flammwidrig nach UL 1581 Section 1060 (FT1), Section 1061 (cable flame), Section 1080 (VW-1) / IEC 60332-1-2 |
| Nominal voltage                 | 300 V                                                                                                        |
| Temperature range (fixed)       | -40...+80 °C                                                                                                 |
| Temperature range (mobile)      | -30...+70 °C                                                                                                 |
| Bend radius (fixed)             | 5× outer Ø                                                                                                   |
| Bend radius (moving)            | 12× outer Ø                                                                                                  |
| No. of bending cycles (C-track) | max. 3 Mio. (25 °C)                                                                                          |
| Traversing distance (C-track)   | max. 5 m (horizontal)                                                                                        |
| Travel speed (C-track)          | max. 3.3 m/s                                                                                                 |
| Acceleration (C-track)          | max. 2 m/s <sup>2</sup>                                                                                      |


**Technical Data**

|                                           |                                                  |
|-------------------------------------------|--------------------------------------------------|
| Operating voltage                         | max. 60 V DC                                     |
| Operating voltage (only UL listed)        | max. 30 V DC                                     |
| Rated surge voltage                       | 1.0 kV                                           |
| Operating current per contact             | max. 1.5 A (20 °C)                               |
| Material group                            | IEC 60664-1, category I                          |
| Transfer parameters                       | CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1) |
| Transfer rate                             | up to 100 Mbit/s full duplex                     |
| LED display                               | no                                               |
| Locking of ports                          | Snap-in connector                                |
| Protection                                | IP20 (RJ45) - IP65, IP67 (RJ45PP)                |
| Locking material                          | Zinc die casting, matte nickel plated            |
| Material                                  | PUR                                              |
| suitable for corrugated tube (internal Ø) | without                                          |



**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444210      |
| EAN                   | 4048879563703 |
| eClass                | 27061801      |
| Packaging unit        | 1             |

**Sketch**



Height: 22 mm



Product may differ from Image