

## **MSUD FORM C 8MM**

PVC 3X0.75 black 30m

MSUD

Form C (8 mm)

24 V AC/DC  $\pm 25\%$

LED



Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

**Illustration**



Product may differ from Image

**Approvals**

cCSAus

\* only for products with UL/GSA approved cable

**Form**

Form

80001

**General data**

Temperature range

-25...+85 °C, depending on cable quality

| Cables                             |  |
|------------------------------------|--|
| No./diameter of wires              | 3 × 0.75 mm <sup>2</sup>                       |
| Wire isolation                     | PVC (bk num, gnye)                             |
| Material (jacket)                  | PVC  |
| Outer Ø                            | 5.9 mm ±5%                                     |
| Bend radius (moving)               | 10 × outer Ø                                   |
| Temperature range (fixed)          | -30...+70 °C                                   |
| Temperature range (mobile)         | -5...+70 °C                                    |
| Cable identification               | 616  |
| Cable Type                         | 1 (PVC)  |
| Approval (cable)                   | CE conform                                     |
| Cable weight [g/m]                 | 61,60  |
| Material (wire)                    | Cu wire, bare                                  |
| Resistor (core)                    | max. 26 Ω/km (20 °C)                           |
| Single wire Ø (core)               | 0.2 mm   |
| Construction (core)                | 24 × 0.2 mm (multi-strand wire class 5)        |
| Diameter (core)                    | 3 × 0.75 mm <sup>2</sup>                       |
| AWG                                | similar to AWG 18                              |
| Material (wire isolation)          | PVC  |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (wire isolation)    | 43 ±5 D  |
| Wire-Ø incl. isolation             | 1.8 mm ±5%                                     |
| Color/numbering of wires           | bk numbered, gnye longitudinally striped       |
| Stranding combination              | 3 wires twisted                                |
| Shield                             | no   |
| Material (jacket)                  | PVC  |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)            | 80 ±5 A  |
| Outer-Ø (jacket)                   | 5.9 mm ±5%                                     |
| Color (jacket)                     | black  |
| chemical resistance                | good resistance to oil, gasoline and chemicals |
| Nominal voltage                    | 300/500 V AC                                   |
| Test voltage                       | 3000 V AC                                      |
| Current load capacity              | to DIN VDE 0298-4                              |
| Temperature range (fixed)          | -30...+70 °C                                   |
| Temperature range (mobile)         | -5...+70 °C                                    |
| Bend radius (fixed)                | 5 × outer Ø                                    |
| Bend radius (moving)               | 10 × outer Ø                                   |
| Jacket Color                       | black  |
| Technical Data                     |  |
| Operating voltage                  | 24 V AC/DC ±25%                                |
| Locking of ports                   | M2.5 (recommended torque 0.4 Nm)               |
| Operating current per contact      | max. 4 A                                       |
| Housing                            | Black plastic (gray on request)                |
| Protection                         | IP67 inserted and tightened (EN 60529)         |
| Commercial data                    |  |
| country of origin                  | CZ   |
| customs tariff number              | 85444290                                       |

EAN 4048879339568

---

eClass 27279218

---

Packaging unit 1