

**RJ45 Push Pull male 0° with cable Profinet**

PUR 2x2xAWG22 shielded gn UL/CSA+dragchain 75m

Male straight  
RJ45PP, 4-pole  
shielded  
Ethernet 10/100 Mbit/s; Push Pull RJ45 Data connector  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

**[Link to Product](#)**

**Illustration**



Product may differ from Image

**Approvals**



\* only for products with UL/CSA approved cable

**More Info**



**Form**

Form 74601

**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Pollution Degree  | 3                                        |
| Temperature range | -25...+85 °C, depending on cable quality |

**Cables**

|                            |                                     |
|----------------------------|-------------------------------------|
| No./diameter of wires      | 2× 2× 0.34 mm <sup>2</sup>          |
| Wire isolation             | PE (wh, ye, bl, or)                 |
| C-track properties         | 3 Mio.                              |
| Jacket Color               | green                               |
| Material (jacket)          | PUR (UL/CSA)                        |
| Outer Ø                    | 6.7 mm ±5%                          |
| Bend radius (moving)       | 12× outer Ø                         |
| Temperature range (fixed)  | -40...+80 °C                        |
| Temperature range (mobile) | -30...+70 °C                        |
| Cable identification       | 796                                 |
| Approval (cable)           | UL (AWM-Style 20233/11602), CSA; CE |
| Cable weight [g/m]         | 69,3                                |

|                                 |                                                                                                              |
|---------------------------------|--------------------------------------------------------------------------------------------------------------|
| Material (wire)                 | Cu wire, bare                                                                                                |
| Resistor (core)                 | max. 55 $\Omega$ /km (20 °C)                                                                                 |
| Diameter (core)                 | 2× 2× AWG22                                                                                                  |
| Material (wire isolation)       | PE                                                                                                           |
| Wire-Ø incl. isolation          | 1.4 mm ±5%                                                                                                   |
| Color/numbering of wires        | wh, ye, bl, or                                                                                               |
| Shield                          | yes                                                                                                          |
|                                 | min. 85%                                                                                                     |
| Material (jacket)               | PUR                                                                                                          |
| Outer-Ø (jacket)                | 6.7 mm ±5%                                                                                                   |
| Color (jacket)                  | green                                                                                                        |
| thermal resistance              | flammwidrig nach UL 1581 Section 1060 (FT1), Section 1061 (cable flame), Section 1080 (VW-1) / IEC 60332-1-2 |
| Nominal voltage                 | 300 V                                                                                                        |
| Temperature range (fixed)       | -40...+80 °C                                                                                                 |
| Temperature range (mobile)      | -30...+70 °C                                                                                                 |
| Bend radius (fixed)             | 5× outer Ø                                                                                                   |
| Bend radius (moving)            | 12× outer Ø                                                                                                  |
| No. of bending cycles (C-track) | max. 3 Mio. (25 °C)                                                                                          |
| Traversing distance (C-track)   | max. 5 m (horizontal)                                                                                        |
| Travel speed (C-track)          | max. 3.3 m/s                                                                                                 |
| Acceleration (C-track)          | max. 2 m/s <sup>2</sup>                                                                                      |


**Technical Data**

|                                           |                                                        |
|-------------------------------------------|--------------------------------------------------------|
| Operating voltage                         | max. 60 V DC                                           |
| Operating voltage (only UL listed)        | max. 30 V DC                                           |
| Rated surge voltage                       | 1.0 kV                                                 |
| Operating current per contact             | max. 1.76 A                                            |
| Material group                            | IEC 60664-1, category I                                |
| Transfer parameters                       | CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)       |
| Transfer rate                             | up to 100 Mbit/s full duplex                           |
| Locking of ports                          | Push Pull                                              |
| Protection                                | IP65 and IP67 when plugged and screwed down (EN 60529) |
| Locking material                          | Zinc die casting, matte nickel plated                  |
| suitable for corrugated tube (internal Ø) | without                                                |


**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444210      |
| EAN                   | 4048879486217 |
| eClass                | 27061801      |
| Packaging unit        | 1             |

**Sketch**



Height: 22 mm



Male

6 321



Product may differ from Image