


**MQ15-X-Power female 0° shielded with cable**

PUR 4x2,5+2x1,5 shielded or UL/CSA+drag chain 30m

Female straight  
MQ15, 6-pole  
shielded  
without cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

[Link to Product](#)

Illustration



Product may differ from Image

Form

Form P8321

General data

|                            |                                          |
|----------------------------|------------------------------------------|
| Mounting method            | inserted, tightened                      |
| Material (contact carrier) | PA                                       |
| Material (contact)         | Copper alloy                             |
| Material (contact surface) | Ag                                       |
| Stripping length (jacket)  | 30 mm                                    |
| Pollution Degree           | 3                                        |
| Temperature range          | -25...+80 °C, depending on cable quality |

Cables

|                            |                                                          |
|----------------------------|----------------------------------------------------------|
| No./diameter of wires      | 4 × 2.5 + 2 × 1.5 mm²                                    |
| Wire isolation             | TPM (bk num, gnye)                                       |
| C-track properties         | 5 Mio.                                                   |
| Jacket Color               | orange                                                   |
| Material (jacket)          | PUR (UL)                                                 |
| Outer Ø                    | 12.8 mm ±5%                                              |
| Bend radius (moving)       | 10 × outer Ø                                             |
| Temperature range (fixed)  | -25...+80 °C                                             |
| Temperature range (mobile) | -20...+80 °C                                             |
| Cable identification       | P11                                                      |
| Material (wire)            | Cu wire, bare                                            |
| Resistor (core)            | max. 14 Ω/km (1.5 mm²), max. 8.5 Ω/km (2.5 mm²); (20 °C) |

|                               |                                          |
|-------------------------------|------------------------------------------|
| Construction (core)           | multi-strand wire class 5 (EN 60228)     |
| Diameter (core)               | 4 × 2.5 + 2 × 1.5 mm <sup>2</sup>        |
| Material (wire isolation)     | TPM                                      |
| Color/numbering of wires      | bk numbered, gnye longitudinally striped |
| Shield                        | yes                                      |
| Material (jacket)             | PUR                                      |
| Outer-Ø (jacket)              | 12.8 mm ±5%                              |
| Color (jacket)                | orange                                   |
| thermal resistance            | flame retardant                          |
| Nominal voltage               | 1000 V AC                                |
| Test voltage                  | 4000 V                                   |
| Temperature range (fixed)     | -40...+80 °C                             |
| Temperature range (mobile)    | -20...+80 °C                             |
| Bend radius (fixed)           | 5 × outer Ø                              |
| Bend radius (moving)          | 10 × outer Ø                             |
| Traversing distance (C-track) | max. 5 m (horizontal)                    |
| Travel speed (C-track)        | max. 3 m/s                               |
| Acceleration (C-track)        | max. 5 m/s <sup>2</sup>                  |
| Torsion stress                | ±15 °/m                                  |


**Technical Data**

|                               |                                                 |
|-------------------------------|-------------------------------------------------|
| Operating voltage             | max. 600 V AC (Power); max. 63 V AC/DC (Signal) |
| Rated surge voltage           | 4.0 kV                                          |
| Operating current per contact | max. 16 A (Power); max. 10 A (Signal)           |
| No. of poles                  | 6                                               |
| LED display                   | no                                              |
| Locking of ports              | Quick connection, 1/4 turn                      |
| Protection                    | IP67 inserted and tightened (EN 60529)          |
| Material                      | Flame retardant plastic acc. to (UL 94)         |
| Mating cycles                 | ≥ 500                                           |
| Configuration                 | fully used                                      |
| Material group                | IEC 60664-1, category I                         |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879710190 |
| eClass                | 27279221      |
| Packaging unit        | 1             |

**Sketch**



Product may differ from Image