


**M12 LITE FEMALE 0°**

PUR 4X0.34 black UL/CSA, drag ch 7.5m

Female straight  
M12, 4-pole  
7005 - plastic hexagonal screw (M12 Lite)  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

**Link to Product**

**Illustration**



Product may differ from Image

**Approvals**





\* only for products with UL/CSA approved cable

**Form**

Form 12221

**General data**

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards                          | DIN EN 61076-2-101 (M12)                                                                                                                               |
| Pollution Degree                   | 3                                                                                                                                                      |
| Temperature range                  | -25...+85 °C, depending on cable quality                                                                                                               |
| <b>Cables</b>                      |                                                                                                                                                        |
| No./diameter of wires              | 4× 0.34 mm <sup>2</sup>                                                                                                                                |
| Wire isolation                     | PP (br, wh, bl, bk)                                                                                                                                    |
| C-track properties                 | 10 Mio.                                                                                                                                                |
| Material (jacket)                  | PUR (UL/CSA)                                                                                                                                           |
| Outer Ø                            | 4.5 mm ±5%                                                                                                                                             |
| Bend radius (moving)               | 10× outer Ø                                                                                                                                            |
| Temperature range (fixed)          | -40...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -25...+80 °C                                                                                                                                           |
| Cable identification               | 634                                                                                                                                                    |
| Cable Type                         | 3 (PUR)                                                                                                                                                |
| Approval (cable)                   | cURus (AWM-Style 20549/10493); CE conform                                                                                                              |
| Cable weight [g/m]                 | 36,30                                                                                                                                                  |
| Material (wire)                    | Cu wire, bare                                                                                                                                          |
| Resistor (core)                    | max. 57 Ω/km (20 °C)                                                                                                                                   |
| Single wire Ø (core)               | 0.1 mm                                                                                                                                                 |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)                                                                                                                 |
| Diameter (core)                    | 4× 0.34 mm <sup>2</sup>                                                                                                                                |
| AWG                                | similar to AWG 22                                                                                                                                      |
| Material (wire isolation)          | PP                                                                                                                                                     |
| Material property (wire isolation) | CFC-, halogen-, cadmium-, silicone- and lead-free                                                                                                      |
| Shore hardness (wire isolation)    | 70 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl, wh                                                                                                                                         |
| Stranding combination              | 4 wires twisted                                                                                                                                        |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR                                                                                                                                                    |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 90 ±5 A                                                                                                                                                |
| Outer-Ø (jacket)                   | 4.5 mm ±5%                                                                                                                                             |
| Color (jacket)                     | black                                                                                                                                                  |
| chemical resistance                | good resistance to oil, gasoline and chemicals (EN 60811-404)                                                                                          |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2                                                                                     |
| Nominal voltage                    | 300 V AC                                                                                                                                               |
| Test voltage                       | 2500 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -40...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                  |
| Temperature range (mobile)         | -25...+80 °C, (+90 °C at max. 10 000 operating hours)                                                                                                  |
| Bend radius (fixed)                | 5× outer Ø                                                                                                                                             |
| Bend radius (moving)               | 10× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 10 Mio. (25 °C)                                                                                                                                   |
| Travel speed (C-track)             | max. 3 m/s                                                                                                                                             |
| Acceleration (C-track)             | max. 10 m/s <sup>2</sup>                                                                                                                               |
| Torsion stress                     | ±180°/m                                                                                                                                                |
| No. of torsion cycles              | max. 2 Mio. (25 °C)                                                                                                                                    |

|               |               |
|---------------|---------------|
| Torsion speed | 35 cycles/min |
|---------------|---------------|

|              |       |
|--------------|-------|
| Jacket Color | black |
|--------------|-------|

**Technical Data**

|                   |                  |
|-------------------|------------------|
| Operating voltage | max. 250 V AC/DC |
|-------------------|------------------|

|                                    |                 |
|------------------------------------|-----------------|
| Operating voltage (only UL listed) | max. 30 V AC/DC |
|------------------------------------|-----------------|

|                               |          |
|-------------------------------|----------|
| Operating current per contact | max. 4 A |
|-------------------------------|----------|

|                     |        |
|---------------------|--------|
| Rated surge voltage | 2.5 kV |
|---------------------|--------|

|                |                         |
|----------------|-------------------------|
| Material group | IEC 60664-1, category I |
|----------------|-------------------------|

|        |         |
|--------|---------|
| Coding | A-coded |
|--------|---------|

|                  |                                                                  |
|------------------|------------------------------------------------------------------|
| Locking of ports | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
|------------------|------------------------------------------------------------------|

|                   |            |
|-------------------|------------|
| Compression gland | M12 (SW13) |
|-------------------|------------|

|            |                   |
|------------|-------------------|
| Protection | IP65, IP66K, IP67 |
|------------|-------------------|

|                  |    |
|------------------|----|
| Locking material | PA |
|------------------|----|

|          |     |
|----------|-----|
| Material | PUR |
|----------|-----|

|                                           |       |
|-------------------------------------------|-------|
| suitable for corrugated tube (internal Ø) | 10 mm |
|-------------------------------------------|-------|

**Commercial data**

|                   |    |
|-------------------|----|
| country of origin | DE |
|-------------------|----|

|                       |          |
|-----------------------|----------|
| customs tariff number | 85444290 |
|-----------------------|----------|


|     |               |
|-----|---------------|
| EAN | 4048879110204 |
|-----|---------------|

|        |          |
|--------|----------|
| eClass | 27279218 |
|--------|----------|

|                |   |
|----------------|---|
| Packaging unit | 1 |
|----------------|---|

**Sketch**

Female



Product may differ from Image