


M23 SERVO CABLE

specification: 6FX5002-5CG01-1BF0

- Female straight
- Plastic housings with good resistance against chemicals and oils.
- M23, 6-pole
- 4-pole used
- shielded
- without brake wires
- Power cable for SINAMICS S120 and Motors with M23 connection
- Mounting bracket
- without cable sleeves
- Further cable lengths on request.

Link to Product




Product may differ from Image

Form	
Form	PS206
General data	
Pollution Degree	3
Temperature range	-25...+85 °C, depending on cable quality
Cables	
Cable number	869
No./diameter of wires	(4G2.5+C)
Wire isolation	PP (bk num, gnye)
C-track properties	0.1 Mio.
Torsion stress	±30 °/m
Jacket Color	orange
Material (jacket)	PVC (UL/CSA) (=MC500)
Specification	6FX5008-1BB21
Outer Ø	9.6 mm ±5%
Bend radius (fixed)	5× outer Ø
Bend radius (moving)	18× outer Ø
Temperature range (fixed)	-25...+80 °C
Temperature range (mobile)	-5...+60 °C
Shield	yes

Approval (cable)	UL (AWM-Style 2570/10492), CSA
Diameter (core)	4× 2.5 mm²
Technical Data	
Operating voltage	max. 630 V AC/DC
Rated surge voltage	6.0 kV
Operating current per contact	Power cores: 12 A (1.5 mm²), 15 A (2.5 mm²)
Material group	IEC 60664-1, category I
Locking of ports	Screw thread (M23×1 mm) recommended torque 2.0 Nm, self-securing
Compression gland	M23 (SW27)
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Locking material	Brass, nickel plated
Material	PUR
suitable for corrugated tube (internal Ø)	16 mm
Commercial data	
country of origin	DE
customs tariff number	85444290
EAN	4048879693554
eClass	27279218
Packaging unit	1
Sketch	

Female



Product may differ from Image