

DRIVE CLIQ CABLE

Specification: 6FX2002-1DC00-1AC0

DRIVE-CLiQ-System

Male straight – male straight


DRIVE-CLiQ IP20 – DRIVE-CLiQ IP20, 10-pole

Further cable lengths on request.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Form

Form SS021

General data

Pollution Degree 3

Temperature range -20...+80 °C, depending on cable quality

Cables

Cable number 884

No./diameter of wires 2 × 2 × 0.22 mm²

Wire isolation PE (gn, ye, pk, bl)

Jacket Color gray

Material (jacket) PVC (UL/CSA)

Specification 6FX2008-1DC00

Outer Ø 6.9 mm ±5%

Bend radius (fixed) 7.5 × outer Ø

Bend radius (moving) 15 × outer Ø

Temperature range (fixed) -20...+80 °C

Temperature range (mobile) 0...+60 °C

Shield yes

Technical Data


Operating voltage max. 30 V AC/DC

Rated surge voltage 0.5 kV

Operating current max. 1.76 A

Material group IEC 60664-1, category II

Locking of ports	DRIVE-CLiQ-System
Protection	IP20
Commercial data	
country of origin	DE
customs tariff number	85444210
EAN	4048879524339
eClass	27061801
Packaging unit	1
Sketch	



Product may differ from Image