

Mico Pro electronic circuit protection, 1 channel

IN: 24 V DC OUT: 24 V DC / 16 A


Mico Pro® fix 1.16

1 channel

Current adjustment 16 A

ATTENTION: Note permissible installation variants

Build your own Mico Pro® online:

<https://micopro.murrelektronik.com>**Link to Product****Illustration**

Product may differ from Image

Approvals**Input**

Operating voltage	12 V DC; 24 V DC (9...30 V DC)
Total current	max. 40 A

Output	
Current adjustment	16 A
No. of channels	1
Inrush capacity	max. 30 mF
Tolerance	0...+20%
Parallel usage/serial usage	-/Selectivity in 2 levels
Control inputs	
Input voltage (ON)	via power module
Impulse length (ON)	via power module
Input voltage (CTRL)	via power module
Impulse length (CTRL)	via power module
Control outputs	
Group alarm output	via power module
Early warning (90%)	via power module
General data	
Protection	IP20
Bridging concept	Bridge set (max. 40 A)
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-25...+55 °C (storage temperature -40...+80 °C)
Dimensions H×W×D	130×12×114 mm
Connections (IN)	
Connection	Bridge system
Connections (OUT)	
Connection	Push-In spring clamp terminals
Cross section (rigid)	0.2...2.5 mm ² (AWG 24...14)
Cross section (flex)	0.2...4 mm ² (AWG 24...12)
Commercial data	
country of origin	CZ
customs tariff number	85363010
EAN	4048879552608
eClass	27141901
Packaging unit	1