

**MICO BASIC 5.2/3.6 ELEC AUX CIRCUIT, 8 CHANNELS**

IN: 24VDC OUT: 5x24V/2ADC 3x24V/6ADC

MICO BASIC 5.2/3.6

8 channels

Current adjustment 5 × 2 A; 3 × 6 A

[Link to Product](#)**Illustration**

Product may differ from Image

**Approvals****Input**

Operating voltage 24 V DC (18...30 V DC)

**Output**

Current adjustment 5 × 2 A; 3 × 6 A

Inrush capacity max. 20 mF (per channel)

**Control inputs**

Input voltage (ON) 10...30 V DC

Impulse length (ON) min. 20 ms

**Control outputs**

Group alarm output max. 20 mA; high: all channels ON; low: not all channels ON

**General data**

Connection Spring clamp terminals

Input terminals 1 × 16 mm<sup>2</sup>Output terminals per output 1 × 4 mm<sup>2</sup>Alarm terminals 2.5 mm<sup>2</sup>

Bridging concept one side, with spring clamp terminals or bridge set (max. 40 A)

Mounting method DIN-rail mountable TH35 (EN 60715)



Dimensions H×W×D 90×70×80 mm

Temperature range 0...+55 °C (storage temperature -40...+80 °C)

#### Commercial data

country of origin	CZ
customs tariff number	85363030
EAN	4048879382373
eClass	27141901
Packaging unit	1

#### Sketch



Product may differ from Image