



Product Benefits

Heavy-Duty Construction –

The most durable heavy-duty dry line field marker available. Dual welded structural steel handles and chassis. Galvanized steel material containers to prevent rusting. 1/2 inch axles and drive shafts for strength. Don't be fooled by the cheap, offshore copies.

Easy to use – Oversized foam rubber hand grips for increased operator comfort. site window to allow view of layout string and chalk dispensing.

Rugged Design – Large 10" no flat tires makes it easy to push even over rocks and rough terrain. Oversized foam rubber handgrips for increased operator comfort.

American Made – Proudly made and assembled in the USA at our Aurora Colorado facility.

TAA compliant

Product Overview

The **Newliner™ HD 50lb. 4 Wheel Dry Line Marker** is the most durable heavy-duty dry line field marker available. The Heavy-Duty liners are made with durable construction to provide years of dependable service. The **Newliner™ HD** is designed for those who want the best, most durable field chalkers available.

The Newliner™ HD 50lb Dry Liner features:

1. Frame has site window to allow view of layout string and chalk dispensing.
2. Four large 10" no flat tires allow for easy pushing even over rough terrain.
3. Loop handle with grips for better control
4. Galvanized steel material containers to prevent rusting.
5. Six-blade paddle for consistent lines
6. Original American made infield chalker.

Specifications

Item Name	Newliner™ HD 50lb 4 Wheel Dry Liner
Item Number	10001744
Application	Medium to large athletic fields
Capacity	50lbs.
Tires/Wheels	Four, 10" pneumatic wheels
Controls	Lever and rod with positive stop plate for precise 2" or 4" wide lines
Dimensions	36"L x 22"W x 22"H
Warranty	18 Months
Shipping weight	55 lbs
Includes	Four 10 inch pneumatic wheels. Oversized foam rubber hand grips for increased operator comfort.