





Scrape & Dry Entrance Mat 137 Opera™

Product Images





Short Description

- Three mat "Scrape & Dry" system in a single mat
- Dense combination of scraping and absorbent yarns ensure maximum performance
- 26 ounces of tufted loop pile yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

Description

A NoTrax® exclusive combines three functional mats into a single mat design. Zone 1 - A looped non-absorbent yarn to scrape debris and moisture. Zone 2 - Combines looped scraper yarns with absorbent Decalon® looped pile to begin the drying process. Zone 3 - Pure Decalon® looped pile to complete the drying function. All yarns are color-coordinated to combine beauty and functionality and is perfectly suited for all large upscale entrances including offices, hotels and professional office buildings.

Specifications

Model No	137
Available Colors	Black; Gray
Overall Thickness	3/8
Standard sizes	3'x 10'; 3'x 12'; 4'x 10'; 4'x 12'; 6'x 10'; 6'x 12'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of offices, shops, restaurants, grocery shops, bakeries, specialty stores.
Special Remarks	A Notrax® exclusive 3-in-1 high performance entrance matting system
Surface	3-Zone System
Edges	Vinyl borders
Usage Intensity	Medium traffic
Backing	Black vinyl (DOP free)
Process	Tufting
Pile Weight Oz	26
Weight Lbs/sqft	0.6
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Superior
Water Retention Rating	Best
Crush Resistance Rating	Best
Function Appearance Rating	Superior

Product Options

Color:	Black
	Gray
Dimensions:	3' X 10'
	3ft x 12ft
	4' X 10'
	4ft x 12ft
	12ft x 6ft