








Moisture & Scrape Entrance Mat Aqua-Trap[®] 150

Product Images







Short Description

- Molded dome pattern facilitates scraping and drying, retaining moisture and debris within its patented Aqua-Dam™ border
- Raised rubber carpet-to-edge (CTE™), bordered on all 4 sides to trap moisture and debris
- Anti-Microbial carpet treatment stops odor causing bacteria and germs
- Molded rubber cleats on the bottom of the mat grip underlying surfaces and minimize mat movement
- 20 ounces of tufted yarn per square yard
- Low profile to perform in narrow clearance doorways

Description

Aqua-Trap® is a unique yet highly functional indoor/outdoor entrance mat with a molded dome pattern that facilitates the scraping and drying process while a patented raised “Aqua Dam™” border forms a perimeter on all four sides of the mat retains moisture and debris. Aqua-Trap® features an antimicrobial carpet treatment that stops odor causing bacteria and germs at the entrance. An extremely durable rubber backed mat, Aqua-Trap® has a highly fashionable look that features carpet-to-the-edge (CTE™) to blend with its surroundings and contemporary color choices to match any décor.

Specifications

Model No	150
Available Colors	Brown; Burgundy; Charcoal; Gray; Hunter Green; Red/Black; Slate Blue
Overall Thickness	3/8
Custom Lengths	3' and 4' widths (5'3" up to 60' long)
Standard sizes	2'x 3'; 3'x 4'; 3'x 5'; 3'x 10'; 4'x 6'; 4'x 10'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of hotels, shops, department stores, schools, universities, restaurants, supermarkets.
Special Remarks	Extremely durable, yet highly fashionable look featuring carpet to-the-edge to blend with its surroundings
Surface	Raised Dome Design
Edges	Fabric covered borders
Usage Intensity	Heavy traffic
Custom Description	Available in stock sizes and in custom lengths. Available colors in charcoal, brown, gray, burgundy, red/black, hunter green, slate blue
Backing	Synthetic rubber
Process	Tufting
Pile Weight Oz	20
Weight Lbs/sqft	1.17
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Superior
Water Retention Rating	Superior
Crush Resistance Rating	Best

Product Options

Color:	Brown
	Burgundy
	Charcoal
	Gray
	Hunter Green
	Red/Black
	Slate Blue
Dimensions:	2' x 3'
	2ft x 3ft
	3' X 4'
	3' X 5'
	3' X 10'
	3ft x 10ft
	3ft x 4ft
	3ft x 5ft
	3ft x Specify Length
	4' X 6'
	4' X 10'
	4ft x 10ft
	4ft x 6ft
	4ft x Specify Length