




Heavy Duty Ramps for Skymaster[®] HD Mats 461

Product Images







Short Description

- Easy to snap together system for on-site custom work station platforms
- Nitrile provides highest level of resistance to chemicals, oils and greases
- Compatible with any of the Skymaster® HD family of mats
- Beveled edges prevent tripping

Description

The Skymaster® HD Ramp is designed for use with the Skymaster® HD family of floor mats and provides a beveled edge for easy access onto or off of the work platform. Made from a 100% nitrile base rubber compound these ramps are made for heavy duty dry industrial environments. All ramp lengths fit the male/female interlocking system of the mats. They are beveled and molded with mitered corners and a protruding tab that locks together for a secure, professional corner.

Specifications

Model No	461
Available Colors	Black; Yellow
Overall Thickness	5/8
Standard sizes	2"x 36"
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals Resistant to most industrial oils
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	All ramp lengths are beveled and molded with mitered corners and a protruding tab. The tab locks together the two adjoining ramps for a secure, professional corner.
Surface	Ribbed
Edges	Attachable beveled edges are available
Usage Intensity	Heavy duty
Material Specifications	100% Nitrile rubber
Process	Compression Molding
Weight Lbs/sqft	1
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Product Options

Color:	Black
	Yellow
Dimensions:	2in x 36in
Variant:	Female
	Male