

Drainage ESD Anti Static Mat Superflow™ XT 555

Product Images





Short Description

- Static dissipative drainage mat removes liquid and debris
- General Purpose Rubber
- Reversible design to extend service life. Lightweight for easy handling and cleaning
- Meets or exceeds requirements of ANSI/ESD S20.20 and per ANSI/ESD STM7.1 and ESD TR53
- Resistance Point to Ground (Rtg): 1×10^6 to 1×10^9 ohms
Resistance Point to Point (Rtt): 1×10^6 to 1×10^9 ohms
- Beveled edges on all 4 sides
- Optional 051 grounding cord available, not required

Description

Superflow™ XT ESD is an Electro Static Discharge (ESD) protective mat that is formulated to drain static electricity from workers to safeguard against static shocks and protect equipment. It is a lightweight anti-fatigue workstation mat available in general purpose rubber compound and its design makes it a perfect choice for applications where the mat is routinely moved for cleaning. Superflow™ XT ESD is reversible further extending the life of the mat. A drainage system facilitates the removal of liquids and debris from the work area and the molded-in beveled edges reduce trip hazards and allow for easy access onto and off of the mat. Superflow™ XT ESD has an aggressive textured top surface that provides additional traction in wet or greasy areas.

Specifications

Model No	555
Available Colors	Black
Overall Thickness	5/8
Standard sizes	2'x 3'; 3'x 5'; 4'x 6'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in ESD assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Reversible design extends the service life - almost like buying two mats for the price of one. Drainage hole size: 1/2"
Surface	Large Drainage Holes
Edges	Molded beveled edges on all sides
Usage Intensity	Medium duty
Custom Description	Available in stock sizes and available black.
Process	Compression Molding
Weight Lbs/sqft	1.3
Fire Rating US	Pass
Anti-Fatigue Rating	Better
Slip Resistance Rating	Best
Wear Resistance Rating	Better

Product Options

Dimensions:

2ft x 3ft

3ft x 5ft

4ft x 6ft