




Diamond Plate Vinyl Runner™, Anti-Slip Mat, 737

Product Images





Short Description

- Heavy-duty vinyl diamond design improves traction and comfort
- Insulates floor and creates a silencing effect
- Oil, grease, and chemical resistant
- Provides barrier to cold floors and floor protection
- Low profile to eliminate trip hazards and allow for cart traffic
- Made of 100% recycled vinyl materials
- Utilizes a vinyl compound

Description

The high profile diamond-embossed top surface yields exceptional traction from any direction. Made of durable vinyl, this runner is easy to sweep clean and has a low profile allowing for easy on/off cart traffic. Diamond Plate Runner™ is recommended for applications where safety and slip protection is needed with minimal anti-fatigue value such as aisles, warehouses, vending areas, and industrial passageways.

Specifications

Model No	737
Available Colors	Black; Black/Yellow; Gray
Overall Thickness	5/32
Roll Sizes	2'x 75'; 3'x 75'; 4'x 75'; 5'x 75'
Custom Lengths	2', 3', 4' and 5' widths (up to 150' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	The diamond plate top surface provides additional traction
Surface	Industrial Diamond Plate
Edges	No borders
Usage Intensity	Medium duty
Material Specifications	PVC
Process	Calendering
Weight Lbs/sqft	0.9
Fire Rating US	Pass
Anti-Fatigue Rating	Good
Slip Resistance Rating	Better
Wear Resistance Rating	Better

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For

more information, visit www.P65Warnings.ca.gov.

Product Options

Color:	Black
	Black/Yellow
	Gray
Dimensions:	2ft x 75ft
	2ft x Specify Length
	3ft x 75ft
	3ft x Specify Length
	4ft x 75ft
	4ft x Specify Length
	5ft x 75ft
	5ft x Specify Length