



# Red Drainage Anti Slip Mat Tek-Tough® T13RD

## Product Images



## Short Description

- Raised edging around each hole creates a slip resistant surface
- Large drainage holes remove liquid and debris from platform
- 100% Nitrile Grease Resistant
- Provides superior ergonomic comfort and traction in wet or greasy areas
- Free of DOP, DMF, ozone depleting substances, silicone and heavy metals
- 7 year warranty

## Description

---

Tek-Tough® is an all purpose anti-fatigue mat for the food service industry available in general purpose (black) and 100% heavy-duty Nitrile (red) rubber compounds for varying degrees of grease and oil protection. Tek-Tough® is designed to provide excellent foot comfort and sure traction in wet or greasy areas. Its' large hole drainage system facilitates the removal of liquids and debris from the work area further enhancing the slip resistance of the mat.

## Specifications

---

Model No	T13RD
Available Colors	Red
Overall Thickness	7/8
Standard sizes	2'x 3'; 3'x 3'; 3'x 5'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Greasy Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	Restaurant kitchens, food prep, food processing environments
Special Remarks	Cleaning with detergent and power-washer is recommended for extended service life
Surface	Large Drainage Holes
Edges	No borders
Usage Intensity	Heavy duty
Material Specifications	100% Nitrile rubber
Process	Compression Molding
Weight Lbs/sqft	2.3
Fire Rating US	Pass
Slip Resistance Rating	Best
Comfort Rating	Superior
Grease Resistance Rating	Superior
Wearability Rating	Superior

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm, and 2-mercaptobenzothiazole which is know

to the State of California to cause cancer. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

## Product Options

---

Dimensions:	2ft x 3ft
	3ft x 3ft
	3ft x 5ft