







# Drainage Red Anti Slip Mat Multi Mat™ II T23RD

## Product Images





## Short Description

---

- Non-skid surface for added traction
- Reversible for extended life
- Low profile for easy cart access
- Nitrile Grease Resistant

## Description

---

Multi-Mat II™ is a reversible drainage mat that offers anti-slip traction in wet or greasy areas. Made from general purpose (Black) and heavy-duty nitrile (Red) rubber compounds for varying degrees of grease and oil protection, Multi-Mat II™ is available in sheet sizes or rolls for longer length application requirements. Its reversible construction design adds to the service life of the mat and a drainage system removes liquids from the work area. A low profile allows for easy cart access.

## Specifications

---

Model No	T23RD
Available Colors	Red
Overall Thickness	3/8
Roll Sizes	2'x 30'; 2'x 32'; 2'x 60'; 3'x 32'; 3'x 64'; 4'x 30'; 4'x 32'; 4'x 64'
Standard sizes	2'x 3'; 2'x 8'; 3'x 4'; 3'x 8'; 4'x 8'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Greasy Areas
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Exceptional non-slip properties in a reversible mat - double the service life.
Surface	Perforated Drainage Pattern
Edges	No borders
Usage Intensity	Medium duty
Material Specifications	75% Nitrile rubber
Process	Compression Molding
Weight Lbs/sqft	1.2
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Slip Resistance Rating	Superior
Comfort Rating	Good
Grease Resistance Rating	Superior
Wearability Rating	Better

## Product Options

---

Dimensions:	2ft x 30ft
	2ft x 32ft
	2ft x 3ft
	2ft x 60ft
	2ft x 8ft
	3ft x 32ft
	3ft x 4ft
	3ft x 64ft
	3ft x 8ft
	4ft x 30ft
	4ft x 32ft
	4ft x 64ft
	4ft x 8ft