
32" x 39", Black, Finger Scrape® Moisture Trap Entry Scraper Mat, T28

Product Images

Short Description

- Tough rubber compound remains flexible while withstanding extreme cold
- Thousands of flexible rubber fingers sweep shoes clean
- Vertical grip lines on the underside of the mat minimize shifting
- Molded beveled edging on all 4 sides creates a retention dam to trap moisture while reducing trip hazards

Description

Finger Scrape® mats are constructed of tough SBR rubber to remain flexible while withstanding extreme cold. Thousands of tough, flexible rubber fingers sweep shoes clean while vertical grip lines on the underside of the mat help to minimize shifting. Due to its durable construction, Finger Scrape® is the perfect year round outdoor entrance mat for schools, municipal buildings, plant entrances, and office buildings.

Specifications

Model No	T28S3239BL
Color	Black
Dimensions	32in x 39in
Thickness	1/4in
UPC	662641802704
Brand	NoTrax
Standard sizes	24"x32", 32"x39", 36"x60", 36"x74"
Group	Entrance Matting
Environment	Outdoor
Special Characteristics	Suitable for use in extreme weather
Special Remarks	Be sure to check door clearance
Edges	Beveled edges on all sides
Usage Intensity	Medium traffic
Material Specifications	Natural rubber
Surface Detail	Flexible Rubber Bristles
Process	Compression Molding
Pallet Quantity	42
Weight Lbs/sqft	1.6
Thickness Inch	1/4in
Dirt Scraping Rating	Superior
Outdoor Use Rating	Better
Wearability Rating	Best

Prop 65

 **WARNING:** This product can expose you to di-2-ethylhexyl phthalate which is known to the State of

California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.