


# Male Branch Tee

## MMS

Male pipe thread / female pipe thread  
SAE 140425

All dimensions are in inches




TUBE FITTING PART #	HOSE FITTING PART #	PTm PORT THD NPTF	PTf PORT THD NPTF	D DRILL (inch)	REF D1 DRILL (inch)	N (inch)	N1 (inch)	XX AFTER ASSY (inch)	Y (inch)	STANDARD MATERIAL FROM STOCK		
										S	SS	B
1/8 MMS	212T-2-2	1/8-27	1/8-27	0.188	0.328	0.78	0.66	0.55	9/16	•	•	•
1/4 MMS	212T-4-4	1/4-18	1/4-18	0.281	0.422	1.09	0.88	0.75	3/4	•	•	•
3/8 MMS	212T-6-6	3/8-18	3/8-18	0.406	0.563	1.22	1.02	0.87	7/8	•	•	•
1/2 MMS	212T-8-8	1/2-14	1/2-14	0.531	0.688	1.47	1.23	1.01	1 1/16	•	•	•
3/4 MMS	212T-12-12	3/4-14	3/4-14	0.719	0.891	1.59	1.36	1.11	1 5/16	•	•	•
1 MMS	212T-16-16	1-11 1/2	1-11 1/2	0.938	1.125	1.97	1.63	1.40	1 5/8	•	•	•

# Male Run Tee

## MRO

Male pipe thread / female pipe thread  
SAE 140424

All dimensions are in inches



TUBE FITTING PART #	HOSE FITTING PART #	PTm PORT THD NPTF	PTf PORT THD NPTF	D DRILL (inch)	REF D1 DRILL (inch)	N (inch)	N1 (inch)	XX AFTER ASSY (inch)	Y (inch)	STANDARD MATERIAL FROM STOCK		
										S	SS	B
1/8 MRO	012T-2-2	1/8-27	1/8-27	0.188	0.328	0.78	0.66	0.55	9/16	•	•	•
1/4 MRO	012T-4-4	1/4-18	1/4-18	0.281	0.422	1.09	0.88	0.75	3/4	•	•	•
3/8 MRO	012T-6-6	3/8-18	3/8-18	0.406	0.563	1.22	1.02	0.87	7/8	•	•	•
1/2 MRO	012T-8-8	1/2-14	1/2-14	0.531	0.688	1.47	1.23	1.01	1 1/16	•	•	•
3/4 MRO	012T-10-10	3/4-14	3/4-14	0.719	0.891	1.59	1.36	1.11	1 5/16	•	•	•
1 MRO	012T-16-16	1-11 1/2	1-11 1/2	0.938	1.125	1.97	1.63	1.40	1 5/8	•	•	•
1 1/4 MRO	012T-20-20	1 1/4-11 1/2	1 1/4-11 1/2	1.250	1.469	2.38	1.70	1.11	1 7/8	•	•	•
1 1/2 MRO	012T-24-24	1 1/2-11 1/2	1 1/2-11 1/2	1.500	1.719	2.64	2.08	2.05	2 1/2	•	•	•