


Interchange Element Data Sheet

Data sheet created using the Parker Par Fit Toolkit software.

Creation Date:	02/10/2018
Datasheet No:	
Parker Part No:	940855Q
OEM:	Parker Original
OEM Part No:	80CN-2

Product Dimensions

B (mm)	55.9	(inch)	2.20
D (mm)	96.5	(inch)	3.80
E (mm)	335.3	(inch)	13.20



Construction Materials

Seal(s):	FKM: Fluorocarbon
Top Endcap:	Glass reinforced nylon
Bottom Endcap:	Glass reinforced nylon
Inner Support Cylinder:	N/A
Filter Media:	Multilayer fiberglass with PBT mesh on both sides

Calculated Performance Criteria

Differential Pressure (Δp):	0.01 bar @ l/min
Tested to ISO3968 @ 32 cSt	0.08 psi @ gpm
Efficiency	>Beta 200 @ 5 microns & greater >Beta 1000 @ 7 microns & greater
Minimum Collapse Pressure:	>10 bar
Tested to ISO2941	>150 psi
Dirt Holding Capacity acc. to ISO16889	