

## Audible Signal Devices

Patlite offers a wide range of audible signal devices for either installation panel or surface mount applications with a variety of decibel ranges and options. All options come with pre-configured digital audio tones and the ability to be field configured using an SD card.

- Up to 110db (signal horn)
- Temperature tolerant (typically -10°C or less to +50°C or more)
- Good environmental protection ratings when installed correctly
- Wide range of digital tones to choose from
- Optional SD card can be used to field configure tones
- Variety of models for both AC and DC applications
- Polycarbonate or plastic construction

## Audible Accessories

Accessories for Patlite audible signal devices:

- Replacement parts
- 2GB micro SD card with SD adapter



# PATLITE® Audible Alarm Buzzers

## Panel-mount Electronic Buzzers

### BM Series Buzzer Features

- Available in both AC and DC versions
- 30mm round mounting on 50mm square backing
- Two selectable alarm sounds
- Up to 90dB volume
- Meets IP30 standards
- Designed to operate in temperatures from -10 to 60°C [14 to 140°F]




**BM-202H**

### BM Series Buzzer Specifications

Part Number	BM-202H	BM-212H
Price	\$36.00	\$36.00
Drawing Link	<a href="#">PDF</a>	<a href="#">PDF</a>
Description	Buzzer	
Rated Voltage	24V AC/DC	120VAC
Operating Voltage Range	Rated voltage $\pm$ 10%	
Rated Power Consumption	0.4 W	2.5 W
Maximum Volume	85dB @ 1m	90dB @ 1m
Tone Type	Buzzer 1: Slow intermittent Buzzer 2: Fast intermittent	
Operating Temperature	-10 to 60°C [14 to 140°F]	
Operating Ambient Humidity	Less than 85% (no condensation)	
Mounting Location	Indoors	
Mounting Direction	Upright, sideways, upside-down	
Protection	IP30 (IEC 60529)	
Insulation Resistance	More than 1M $\Omega$ at 500VDC between terminals and chassis	
Withstand Voltage	500VAC applied for 1 minute between terminals and chassis	1500VAC applied for 1 minute between terminals and chassis
Weight	100g [3.5 oz]	
Housing Material	ABS Plastic	
Agency Approvals	EMC Directive (EN 55011, EN 610006-2) RoHS Directive (EN 50581) Conforms to CE requirements	-

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Wiring Diagram



# PATLITE® Audible Signal Horns

## Electronic Sound Signal Horns

### EHS Series Horns Features

- Compact signal horn
- Four playback modes
- Can be used with either PNP or NPN inputs
- Meets IP65 standards
- Designed to operate in temperatures from -20 to 50°C [-4 to 122°F]
- Polycarbonate construction
- 32 standard sounds
- Optional SD card for field configuration (sold separately)



**EHS-M1TE**



**V21100522-F1**




**V13100076-F1**

EHS Series Signal Horns Specifications		
Part Number	EHS-M1TE	EHS-M2TE
Price	\$245.00	\$245.00
Drawing Link	<a href="#">PDF</a>	<a href="#">PDF</a>
Description	Signal Horn	
Rated Voltage	12-24VDC	100-240VAC (50/60Hz)
Operating Voltage	10.8-35 VDC	90-264VAC (50/60Hz)
Current Consumption	450mA	140mA
Power Consumption	5.0-7.6 W	6.9-7.3 W
Inrush Current	4-12.5 A or less	6-23 A or less
Maximum Volume	110dB @ 1m	
Tone Type	Electronic (32 tones available)	
Operating Temperature	-20 to 50°C [-4 to 122°F]	
Operating Ambient Humidity	Less than 85% (no condensation)	
Mounting Location	Indoors/outdoors	
Mounting Direction	Upright, sideways, upside-down	
Protection	IP65	
Insulation Resistance	More than 1MΩ at 500VDC between terminals and chassis	
Withstand Voltage	500VAC applied for 1 minute between terminals and chassis	1500VAC applied for 1 minute between terminals and chassis
Vibration Resistance	45.0 m/s2 (IEC 60068-2-6:2007), upright	
Weight	1.25 kg [2.8 lbs]	
Housing Material	Polycarbonate	
Memory Card	SD card (SDV-2GP recommended, sold separately), FAT16 or 32 format	
Agency Approvals	EMC Directive (EN 61000-6-4, EN 6100-6-2)	
	RoHS Directive (EN 50581) UL 464, CSA-C22.2 No. 205-M1983 FCC Part 15 Subpart B Class A KC (KN22, KN24) UL Listed (File S24210)	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

EHS Series Accessories		
Part Number	Price	Description
<a href="#">V21100522-F1</a>	\$33.00	Replacement cover, for EHS series signal horns
<a href="#">V13100076-F1</a>	\$30.50	Replacement 16 inch cable, for EHS series signal horns
<a href="#">SDV-2GP</a>	\$17.50	2GB micro SD card with SD adapter

### WIRING DIAGRAM



# PATLITE® Audible Electronic Alarms

## BD Series Panel- or Surface-mount Electronic Alarms

### Features

- 80mm square alarm
- 32 different alarm tones available
- Up to 90dB volume
- Meets IP54 standards
- Designed to operate in temperatures from -20 to 55°C [-4 to 131°F]
- ABS plastic construction
- 32 standard sounds
- Optional SD card for field configuration (sold separately)




BD-24AE-J

BD Series Accessories		
Part Number	Price	Description
<a href="#">SDV-2GP</a>	\$17.50	2GB micro SD card with SD adapter

BD Series Alarm Specifications		
Part Number	BD-24AE-J	BD-24AE-K
Price	\$120.00	\$120.00
Drawing Link	<a href="#">PDF</a>	<a href="#">PDF</a>
Description	Alarm	
Rated Voltage	12-24VDC	
Operating Voltage Range	10.8-26.4 VDC	
Rated Power Consumption	Standby	0.5 W
	Maximum	4.0 W
Maximum Volume	90dB @ 1m	
Tone Type	Electronic (32 tones available)	
Operating Temperature	-20 to 55°C [-4 to 131°F]	
Operating Ambient Humidity	Less than 85% (no condensation)	
Mounting Location	Indoors	
Mounting Direction	Upright, sideways, inverted	
Protection	IP54	
Insulation Resistance	More than 1MΩ at 500VDC between terminals and chassis	
Withstand Voltage	500VAC applied for 1 minute between terminals and chassis	
Vibration Resistance	19.6 m/s <sup>2</sup> (IEC 60529)	
Weight	160g [5.6 oz]	
Housing Material	ABS plastic	
Housing Color	Light gray	Dark gray
Agency Approvals	EMC Directive (EN 61000-6-4, EN 61000-6-2) RoHS Directive (EN 50581) FCC Part 15, Subpart B Class A UL 464, CSA-C22.2 No. 205-M1983 UL Recognized (File S24210) Conforms to CE requirements	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

### Wiring Diagram



# PATLITE® Audible Electronic Alarms

## BSV Series Panel- or Surface-mount Electronic Alarms

### Features

- Compact alarm that plays 15 prerecorded alarms
- Up to 90dB volume
- Meets IP54 standards when panel mounted
- Works with PNP inputs
- Designed to work in temperatures from -10 to 50°C [14 to 122°F]
- Polycarbonate construction
- 15 standard sounds
- Optional SD card for field configuration (sold separately)



**BSV-24P-D**

BSV Series Accessories		
Part Number	Price	Description
<b>SDV-2GP</b>	\$17.50	2GB micro SD card with SD adapter

BSV Series Alarm Specifications		
Part Number	<i>BSV-24P-D</i>	<i>BSV-24P-W</i>
<b>Price</b>	\$137.00	\$137.00
<b>Drawing Link</b>	<a href="#">PDF</a>	<a href="#">PDF</a>
<b>Description</b>	Alarm	
<b>Rated Voltage</b>	12-24VDC	
<b>Operating Voltage Range</b>	10.8-26.4 VDC	
<b>Rated Power Consumption</b>	3.5 W	
<b>Maximum Volume</b>	85dB @ 1m	
<b>Tone Type</b>	Electronic (15 tones available)	
<b>Operating Temperature</b>	-10 to 50°C [14 to 122°F]	
<b>Operating Ambient Humidity</b>	Less than 85% (no condensation)	
<b>Mounting Location</b>	Panel mount: Indoor/outdoor Wall mount: Indoors	
<b>Mounting Direction</b>	Upright, sideways, inverted	
<b>Protection</b>	Panel mount: IP54 (upright mounting direction only) Wall mount: IP20	
<b>Insulation Resistance</b>	More than 1MΩ at 500VDC between terminals and chassis	
<b>Withstand Voltage</b>	500VAC applied for 1 minute between terminals and chassis	
<b>Vibration Resistance</b>	70.0 m/s <sup>2</sup> (in the x, y, and z directions for 2 hours each at 30Hz)	
<b>Weight</b>	100 [3.5 oz]	
<b>Housing Material</b>	Polycarbonate	
<b>Housing Color</b>	Dark gray	Off-white
<b>Agency Approvals</b>	EMC Directive (EN 61000-6-4, EN 61000-6-2) RoHS Directive (EN 50581) FCC Part 15, Subpart B Class A UL Recognized (File S24210)	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

### Wiring Diagram

