

Spring Retractable Pre-Rinse Reels

Water - 3/8", 1/2" I.D.

Pre-Rinse

- A lever-operated spray valve is included (S600080)
- Optional 360° rotating swivel (600248) offers 20° of angular motion
- Low-pressure 3/8 in. x 35 ft. rubber hose included; rated for hot water up to 180 °F (82 °C)
- The reliable speed latch allows for positive locking of the spool in two positions per rotation
- Guide arm adjusts to two positions



5635 OLPSW5



Interactive Reel Catalog

Visit reelcraft.com/catalog for complete product specifications, parts, and accessories.



Pre-Rinse Spray Valve
S600080



Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Max Pressure		NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index Page	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar	in	in	in		
Pre-Rinse Hose Reels Maximum temperature 180°F (82°C)															
5635 OLPSW5	27	12	3/8	10	.660	17	35	11	125	9	3/8	3/8	1/4	10	1



Pivot Bases & Swing Brackets
See page 39

Stainless Steel Fluid Path Hose Reels

1/2", 3/4", 1" I.D.

- Offers another level of protection in corrosive environments
- Stainless steel swivel and stainless steel main shaft - all components in contact with media
- Cast aluminum ratchet and latch pawl provide reliability and durability
- By design, the ratchet and latch pawl are substantially thicker than competing reels to reduce wear and increase service life
- Steel components are individually powder coated prior to assembly to maximize corrosion resistance



HD79005 OLB



Model without hose & bumper	Shipping Weight		Hose Capacity				Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index Page	Size Index #			
	lbs	kg	I.D.		Length									
Low Pressure Air/Water Reels Maximum Temperature 210°F (99°C)														
HD78005 OLB	54	24	1/2	13	.750	19	75	23	500	35	1/2	1/2	13	2
HD79005 OLB	54	24	3/4	19	1.075	27	50	15	500	35	3/4	3/4	13	2
E9305 OLBBW	115	52	3/4	19	1.075	27	100	30	500	35	3/4	3/4	16	2
E9400 OLBBW	115	52	1	25	1.375	35	50	15	500	35	1	1	16	1



Series 9000 Roller Guide Kits
See page 38



Pivot Bases & Swing Brackets
See page 39