

TRUELINE™

HVACR & WATER HEATER PARTS AND ACCESSORIES

85-4101

HIGH PRESSURE SOLVENT CLEANER

REFRIGERATION CONDENSER CLEANER


- Non-flammable
- Non-conductive
- 32,000 Volt Dielectric
- Contains No Oil
- Leaves No Film

DANGER: KEEP OUT OF REACH OF CHILDREN. HARMFUL OR FATAL IF SWALLOWED. VAPOR HARMFUL. CAUSES SKIN IRRITATION. MAY CAUSE AN ALLERGIC SKIN REACTION. CAUSES SERIOUS EYE IRRITATION. CONTAINS GAS UNDER PRESSURE; MAY EXPLODE IF HEATED. USE ONLY IN WELL VENTILATED AREA. FOR PROFESSIONAL USE ONLY. SEE BACK PANEL FOR ADDITIONAL PRECAUTIONS.

NET WEIGHT. 18 OZ. (510g)



85-4101



6

A highly concentrated solvent designed to blast away dirt, grease, oil and grime from refrigeration and air conditioning condenser coils. Cleaning is quick and effective. Ideally suited for use on condenser coils where water clean-up is a problem.

NOTE: Do NOT allow SOLVENT CLEANER to contact polystyrene foam. Immediate damage will occur. This product may affect certain plastics commonly used for drain pans and other components. Do not allow SOLVENT CLEANER to remain in contact with plastics. Wipe immediately with a cloth or paper towel. Test plastics in an inconspicuous area before use.

DIRECTIONS FOR USE: Use only with adequate ventilation. Disconnect power to equipment. Place rags behind and under coil area being cleaned to collect grease and wet soil that is removed. Spray generously over the surface to be cleaned until completely wet. Allow the solvent to set for a minute, then wipe or rinse off with a second spray.

DANGER: KEEP OUT OF REACH OF CHILDREN. Read label and Safety Data Sheet before use. Contains gas under pressure; may explode if heated. Causes skin irritation. Causes serious eye irritation. May cause an allergic skin reaction. Suspected of causing genetic defects. May cause cancer. May cause drowsiness or dizziness.

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Avoid breathing mist, vapors, or spray. Use only outdoors or in a well-ventilated area. Pressurized container: Do not pierce or burn, even after use. Wash hands and face thoroughly after handling. Wear protective gloves, protective clothing, and eye and face protection. Do not eat, drink or smoke when using this product. Contaminated work clothing should not be allowed out of the workplace.

FIRST AID: IF SWALLOWED: Immediately call a poison center/doctor. Do NOT induce vomiting. Rinse mouth. IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell. IF exposed or concerned: Get medical advice/attention.

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Store in a well-ventilated place. Store locked up.

Dispose of contents/container in accordance with local, regional, national, and international regulations.

WARNING: This product can expose you to chemicals including trichloroethylene, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information, go to www.P65Warnings.ca.gov.

Contains [CAS]: Trichloroethylene [79-01-6], Carbon dioxide (propellant) [124-38-9].

Distributed by: Rheem Parts Division, Randleman, NC

Made in U.S.A.
North American Research Corp.,
PO Box 1318, Lewisville, TX 75067
800-527-7520 • 972-492-1800

