

TRUELINE™

HVACR & WATER HEATER PARTS AND ACCESSORIES

85-H2401

MINERAL REFRIGERATION OIL 300 SUS

**Viscosity 300 SUS (ISO VG 68)
Replaces 4GS**

- For use with CFC and HCFC refrigerants
- Refined from select naphthenic base oils
- Highest quality available
- Excellent low temperature properties
- Long-term, trouble-free service

NET CONT. 1 U.S. GALLON (3.785 L)

This package contains RO-30, manufactured by Calumet Lubricants Co., and meets the specifications of most equipment and compressor manufacturers for applications requiring a 300SUS (ISO VG 68) mineral compressor lubricant.

Consult equipment manufacturer for specific recommendations.

APPLICATION RECOMMENDATIONS

Mineral Refrigeration Oils are recommended for use with CFC, HCFC, and ammonia refrigerants. Do NOT use in systems with HFC refrigerants such as R134a and R410a. ALWAYS FOLLOW THE EQUIPMENT MANUFACTURER'S RECOMMENDATION FOR SELECTION. If none is available, use the following as a guide:

- For refrigerants 11, 12 and 113 with evaporator temperatures above -20°F, use 150 SUS or 300 SUS; below -20°F, use 150 SUS.
- For Refrigerants 13, 22, 114, 502 ethane, propane and isobutane, use 150 SUS.
- For ammonia with evaporator temperatures above -20°F, use 300 SUS or 500 SUS; below -20°F, use 150 SUS.

NOTE: Refrigeration lubricants absorb moisture from air which may be harmful to equipment. Keep container tightly closed when not dispensing.

CAUTION: Keep out of reach of children. For professional use only. Consult Material Safety Data Sheet and read entire label before use.

FIRST AID: Wash skin contact thoroughly with soap and water. Flush eyes with water for 15 minutes. Get medical attention if irritation develops. Avoid repeated and prolonged contact.

**Distributed by: Rheem Parts Division,
Randleman, NC**

Made in U.S.A.
North American Research Corp.,
PO Box 1318, Lewisville, TX 75067
800-527-7520 • 972-492-1800



85-H2401



6 62766 26094 6