



POLYKEN® 227 Contractor Grade Duct Tape


APPLICATIONS

- Sealing metal duct work and fiberglass insulation.
- General purpose packaging.
- Home and general repair.

FEATURES & BENEFITS

- Bonds to all types of surfaces.
- Easily applied.
- Will not twist or curl.
- Tested in accordance with UL 723.
- Contributes toward satisfying EQ Credit 4.1 (Low Emitting Materials Adhesives & Sealants) under LEED®.

CONSTRUCTION



PRODUCT DESCRIPTION

Single-Coated Construction

Backing:

- Polyethylene Coated Cloth

Adhesive:

- Rubber

Colors:

- Silver

TEST DATA

Test	Typical Value	Typical Value (Metric)	Test Method
Total Thickness	11 mils	279.40 μ	ASTM D 1000
Adhesion to Steel	70 oz./in.	7.66 N/cm	PSTC-1
Adhesion to Backing	30 oz./in.	3.28 N/cm	PSTC-1
Tensile Strength	24 lb./in.	42.03 N/cm	ASTM D 1000
Maximum Performance Temperature	200 D F		
Flame Spread	5		
Smoke Developed	15		
VOC Content	<1 g/L		

Recommended storage conditions: 40-60% Humidity, 60°F-80°F

**Products are not reviewed or certified under the LEED® Rating System. LEED® credit requirements cover the performance of materials in aggregate, not the performance of individual products or brands. For more information on LEED®, visit www.usgbc.org/leed.

The information presented herein was prepared at BERRY PLASTICS CORPORATION (25 Forge Parkway Franklin, MA 02038) by qualified technical person. To Berry's knowledge it is true and accurate. However, the information and recommendations are furnished for these products with the understanding that the purchaser or user, as the case may be, will independently determine that the product is suitable for the intended use, and that such use complies with all applicable federal, state and local laws and regulations. The data are submitted only for the user's information and consideration, and do not constitute a warranty of any kind (including but not limited to a warranty of merchantability or of fitness for a particular purpose), or a representation for which BERRY PLASTICS assumes any responsibility.