

STARPOINT VRS-2,3t-G2"

Artikel-Nr: 7900433




Vario-Starpoint VRS with adapter to pipe thread G2" DIN ISO 228-1.

- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts (Version VRS-F).
- For permanent installation and recurrend lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-2,3t-G2"

Artikel-Nr: 7900433



weight	1.89 kg	4.17 lbs
Nominal WLL	2300 kg	5070 lbs
T	73 mm	2-7/8"
B	17 mm	43/64"
C	16 mm	5/8"
D	40 mm	1-9/16"
E	81 mm	3-3/16"
F	70 mm	2-3/4"
I	70 mm	2-3/4"
K	76 mm	3"
L	45 mm	1-25/32"
M	G 2" mm	G 2"
N	12 mm	15/32"