

STARPOINT VRS-0,1t-M6

Artikel-Nr: 7900909




- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Tested and certified by DGUV. Testing specifications: GS-HM-36: 2023-06, Certificate No.: HM 250037
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts (Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-0,1t-M6

Artikel-Nr: 7900909



weight	0.07 kg	0.15 lbs
Nominal WLL	100 kg	220 lbs
T	28 mm	1-1/8"
B	9 mm	11/32"
C	7 mm	9/32"
D	20 mm	3/4"
E	23 mm	29/32"
G	28 mm	1-1/8"
I	13 mm	1/2"
K	37 mm	1-7/16"
L	9 mm	11/32"
M	M 6 mm	M 6
N	6 mm	15/64"