

L-ABA 10000 daN - Lashing point for welding, loadable from any direction

Artikel-Nr: 7901722




- Lashing point that can be loaded on all sides.
- Ideal for pile drivers, drilling equipment, rollers and earthmoving machinery.
- Clear indication of the minimum lashing capacity in daN.
- Forged from a single piece, no rattling noise or shaking.
- The weld arrangement (circular fillet weld) fulfils the requirements of EN 1090, i.e. the endless weld seam prevents the formation of contact/crevice corrosion (thus suitable for outdoor constructions).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lashing points can be found in the specific user instruction.

L-ABA 10000 daN - Lashing point for welding, loadable from any direction

Artikel-Nr: 7901722



weight	2.26 kg	4.98 lbs
T	72 mm	2-2/32"
A	51 mm	2"
B	27 mm	1-1/16"
C	172 mm	6-25/32"
D	60 mm	2-3/8"
E	28 mm	1-1/8"
F	99 mm	3-7/8"
Lashing capacity	10000 daN	null