

## Eye Plate for Corners VRBK-FIX 4t

Artikel-Nr: 7902149




An enhancement of the well-established VRBK - series.

- A forged ring bracket according to EN1677-1, electromagnetically crack detected, pink powder coated and it can be loaded in all directions.
- No time-consuming alignment between the weld-on blocks and ring.
- Clamp spring is protected placed inside the weld-on block.
- The spring fixes the weld-on blocks to the ring and creates at the same time a radial clamping.
- No loose items.
- Clamping spring avoids rattling noise.
- Recognition of inclination angle indicated by markings on the ring and on the blocks in all levels.
- Even force distribution owing to the two point attachment.
- Low profile size it can be folded with in an angle range of 270°.
- The welding block for edges is forged out of a good welding material 1.0577+N (St 52-3) and clearly stamped with an identification number for the permissible WLL.
- Tested and certified by DGUV, Testing specifications: GS-HM-36: 2023-06, Certificate-No.: HM 250039

Welding should only be carried out by qualified persons according to ISO 9606-1.

## Eye Plate for Corners VRBK-FIX 4t

Artikel-Nr: 7902149



<b>weight</b>	1.05 kg	2.31 lbs
<b>Nominal WLL</b>	4000 kg	8820 lbs
<b>T</b>	65 mm	2-9/16"
<b>A</b>	32 mm	1-1/4"
<b>B</b>	14 mm	9/16"
<b>C</b>	28 mm	1-1/8"
<b>D</b>	48 mm	1-7/8"
<b>E</b>	141 mm	5-9/16"
<b>F</b>	30 mm	1-3/16"