

Eye Plate for Corners VRBK-FIX 6,7t

Artikel-Nr: 7902150




An enhancement of the well-established VRBK - series.

- A forged ring bracket according to EN1677-1, electromagnetically crack detected, pink powder coated and it can be loaded in all directions.
- No time-consuming alignment between the weld-on blocks and ring.
- Clamp spring is protected placed inside the weld-on block.
- The spring fixes the weld-on blocks to the ring and creates at the same time a radial clamping.
- No loose items.
- Clamping spring avoids rattling noise.
- Recognition of inclination angle indicated by markings on the ring and on the blocks in all levels.
- Even force distribution owing to the two point attachment.
- Low profile size it can be folded with in an angle range of 270°.
- The welding block for edges is forged out of a good welding material 1.0577+N (St 52-3) and clearly stamped with an identification number for the permissible WLL.
- Tested and certified by DGUV, Testing specifications: GS-HM-36: 2023-06, Certificate-No.: HM 250039

Welding should only be carried out by qualified persons according to ISO 9606-1.

Eye Plate for Corners VRBK-FIX 6,7t

Artikel-Nr: 7902150



weight	2.16 kg	4.76 lbs
Nominal WLL	6700 kg	14770 lbs
T	84 mm	3-5/16"
A	40 mm	1-9/16"
B	20 mm	3/4"
C	35 mm	1-3/8"
D	60 mm	2-3/8"
E	181 mm	7-1/8"
F	34 mm	1-11/32"