

## Lashing point for corners for welding LRBK-FIX 8000 daN

Artikel-Nr: 7903056




- Lift bail with extended pivoting area, can be pivoted through 270°.
- Optimal for edges – saves half the lashing points.
- Clear indication of the lashing capacity in daN.
- Split force introduction thanks to multiple point fixing.
- LC possible up to 90° in load ring plane.
- Thanks to the weld arrangement (circular fillet weld), no contact/crevice corrosion can occur.
- The clamping spring achieves noise reduction and keeps the suspension ring in the desired direction.
- Simple alignment of ring lug.
- Ring lug remains in position.
- Simple painting.

Welding should only be carried out by qualified persons according to ISO 9606-1.

## Lashing point for corners for welding LRBK-FIX 8000 daN

Artikel-Nr: 7903056



<b>weight</b>	1.05 kg	2.31 lbs
<b>T</b>	65 mm	2-9/16"
<b>A</b>	32 mm	1-1/4"
<b>B</b>	14 mm	9/16"
<b>C</b>	28 mm	1-1/8"
<b>D</b>	48 mm	1-7/8"
<b>E</b>	141 mm	5-9/16"
<b>F</b>	30 mm	1-3/16"
<b>Lashing capacity</b>	8000 daN	null