

## VLBS-U-LT 10t - Load ring welded for low temperature -45°C

Artikel-Nr: 7903135




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks. Weld: HV 16 + a 4
- The weld-on-block is made (forged) out of a good weldable steel.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## VLBS-U-LT 10t - Load ring welded for low temperature -45°C

Artikel-Nr: 7903135



<b>weight</b>	2.76 kg	6.08 lbs
<b>Nominal WLL</b>	10000 kg	22040 lbs
<b>T</b>	126 mm	5"
<b>A</b>	75 mm	2-15/16"
<b>B</b>	129 mm	5-1/16"
<b>C</b>	55 mm	2-5/32"
<b>D</b>	67 mm	2-5/8"
<b>E</b>	71 mm	2-13/16"
<b>F</b>	26,5 mm	1-3/64"
<b>G</b>	60 mm	2-3/8"
<b>H</b>	26,5 mm	1-3/64"