

## VLBS-U-LT 4t - Load ring welded for low temperature -45°C

Artikel-Nr: 7903400




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks. Weld: HV 8 + a 3
- The weld-on-block is made (forged) out of a good weldable steel.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## VLBS-U-LT 4t - Load ring welded for low temperature -45°C

Artikel-Nr: 7903400



<b>weight</b>	0.72 kg	1.59 lbs
<b>Nominal WLL</b>	4000 kg	8820 lbs
<b>T</b>	83 mm	3-1/4"
<b>A</b>	42 mm	1-21/32"
<b>B</b>	87 mm	3-7/16"
<b>C</b>	31 mm	1-7/32"
<b>D</b>	51 mm	2"
<b>E</b>	52 mm	2-1/16"
<b>F</b>	18 mm	23/32"
<b>G</b>	46 mm	1-13/16"
<b>H</b>	16 mm	5/8"