

Eye Plate for Corners VRBK-FIX 31,5t

Artikel-Nr: 7906225




An enhancement of the well-established VRBK - series.

- A forged ring bracket according to EN1677-1, electromagnetically crack detected, pink powder coated and it can be loaded in all directions.
- No time-consuming alignment between the weld-on blocks and ring.
- Clamp spring is protected placed inside the weld-on block.
- The spring fixes the weld-on blocks to the ring and creates at the same time a radial clamping.
- No loose items.
- Clamping spring avoids rattling noise.
- Recognition of inclination angle indicated by markings on the ring and on the blocks in all levels.
- Even force distribution owing to the two point attachment.
- Low profile size it can be folded with in an angle range of 270°.
- The welding block for edges is forged out of a good welding material 1.0577+N (St 52-3) and clearly stamped with an identification number for the permissible WLL.
- Tested and certified by DGUV, Testing specifications: GS-HM-36: 2023-06, Certificate-No.: HM 250039

Welding should only be carried out by qualified persons according to ISO 9606-1.

Eye Plate for Corners VRBK-FIX 31,5t

Artikel-Nr: 7906225



weight	24.65 kg	54.34 lbs
Nominal WLL	31500 kg	69440 lbs
T	177 mm	6-31/32"
A	89 mm	3-1/2"
B	42 mm	1-21/32"
C	78 mm	3-1/16"
D	130 mm	5-1/8"
E	394 mm	15-1/2"
F	70 mm	2-3/4"
G	42 mm	1-21/32"