

VLBS-Welding block ASK-VLBS 16t

Artikel-Nr: 7906638




The welding block is forged out of the material 1.0577+N (St 52-3) and is marked with the identification number of the permissible nominal WLL.

The distance lugs have a distance measurement function for the required spacing to the root weld. (approx. 3mm) Welding should be carried out by a qualified person according to ISO 9606-1.

The joint faces must be free from impurities like oil, colour etc. The chosen welding point must be suitable for the corresponding force introduction. The engaging surface must be plain. Given an uneven surface, the weld blocks have to be re-adjusted. Root welding: Beginning of the root weld + fillet weld in the middle of the welding block. Carefully clean the root before placing the covering weld seam. Separate welding instructions for the welding procedure and filler metals are supplied with the VLBS.

VLBS-Welding block ASK-VLBS 16t

Artikel-Nr: 7906638



weight	2.20 kg	4.85 lbs
Nominal WLL	16000 kg	35300 lbs
T	43 mm	1-11/16"
A	96 mm	3-25/32"
B	90 mm	3-17/32"
C	69 mm	2-23/32"