

Load Ring VLBS-U-16t with spring

Artikel-Nr: 7906640




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks. Weld: HV 25 + a 6
- The weld-on-block is made (forged) out of a good weldable steel.
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2023-06, Certificate-No.: HM 240067
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load Ring VLBS-U-16t with spring

Artikel-Nr: 7906640



D	100 mm	3-15/16"
E	106 mm	4-3/16"
F	40 mm	1-9/16"
G	90 mm	3-17/32"
H	26 mm	1"
weight	7.12 kg	15.70 lbs
Nominal WLL	16000 kg	35270 lbs
T	176 mm	6-15/16"
A	96 mm	3-25/32"
B	192 mm	7-9/16"
C	70 mm	2-3/4"