

STARPOINT VRS-16t-M56

Artikel-Nr: 7907508




- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Available as: - Standard Metric Thread (DIN EN 13)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- For permanent installation and recurrend lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-16t-M56

Artikel-Nr: 7907508



weight	11.99 kg	26.43 lbs
Nominal WLL	16000 kg	35270 lbs
T	161 mm	6-11/32"
B	50 mm	1-31/32"
C	44 mm	1-3/4"
D	110 mm	4-11/32"
E	112 mm	4-13/32"
G	145 mm	5-11/16"
I	82 mm	3-1/4"
K	210 mm	8-1/4"
L	84 mm	3-5/16"
M	M56 mm	M56
N	32 mm	1-1/4"